# Reliable

### Model B Model FM Spray Nozzles

Reliable Models B Open Window, FM Open Window and FM Open Cornice Nozzles are especially designed for external use. They are installed in locations where a blanket of water is desired over a predetermined area. Open Nozzle systems can be operated manually or by quick opening valves that are pneumatically, hydraulically or electrically controlled.

All Open Nozzles are available in the following finishes: Bronze, Chrome, lead plated. No waterway protection is provided.

The following table lists Reliable Open Nozzles by type, orifice size, pipe connection size, overall length, installation position and SIN.

Installation positions other than the design installation position shown in the table may be used. However, the resulting distribution pattern in the installed position must be carefully considered.

#### Model B

#### **Open Window Nozzle**

This Nozzle is designed to provide protection for exterior wall, windows and other openings of buildings that may be subjected to fire spreading from neighboring properties. It is usually installed at the top of windows or other openings.

The Model B Open Window Sprinkler may be utilized in the protection of such things as horizontal, multi-tier veneer dryers and structural steel members not requiring fire-resistant insulation. For such uses the authority having jurisdiction should be consulted for the acceptance of the application.

A Model B Open Window Sprinkler distributes water in a fan-shaped pattern against the exterior surface, resulting in a water curtain extending all the way to the ground.

UL Listed, FM Approved.



	Orifice Size (in)	NPT Thread (in)	K Factor		Overall	Installation	Pressure	Distance	Width	Sprinkler
Туре			US	Metric	Length (in)	Position	(psi)	(ft)	(ft)	Identification Number (SIN)
	1/4	1/2	1.81	26	1 <sup>13</sup> / <sub>16</sub>	Pendent	7	8	20	R0413
							53	15	43	
							100	16	42	
	5/16	1/2	2.57	37	<b>1</b> <sup>13</sup> / <sub>16</sub>	Pendent	4	8	22	R0414
Window (Model B)							52	16	40	
							100	17	40	
	3/8	1/2	3.45	50	1 <sup>13</sup> /16	Pendent	4	9	22	
							52	18	40	R0415
							100	17	40	

The Window (Model B) spray nozzles require the use of an individual, integral, or main-line strainer per Factory Mutual Approval Standards.

#### Model FM

#### **Open window Nozzle**

This Nozzle performs the same basic function for the protection of exterior walls and their openings as the Model B Open Window Sprinkler. Having a larger orifice than the Model B Open Window Sprinkler, it distributes a larger volume of water.

FM Approved.



	Orifice Size (in)	NPT Thread (in)	K Factor		Overall	Installation	Pressure		Width	Sprinkler
Туре			US	Metric	Length (in)	Position	(psi)	Angle	(ft)	Identification Number (SIN)
	3/4	3/4	14.4	207	3	Pendent	7	150	16	R0411
							52	150	20+	
							100	151	20+	
							7	149	11	R0416
Window (Model FM)	5/8	3/4	10.0	144	3	Pendent	52	150	20+	
(,							100	150	20+	
							7	119	9	
	1/2	1/2	6.6	95	3	Pendent	52	121	15	R0418
							100	119	15	

## Model FM Open Cornice Nozzle

This Nozzle is installed under building cornices and ridges to provide protection for these exterior surfaces. Because of the special contour of the deflector, it distributes water equally on opposite sides in a narrow fan-shaped curtain. The distribution pattern covers the underside of cornices and ridges with water.



Model FM Cornice

#### FM Approved.

	Туре	Orifice Size (in)	NPT Thread (in)	K Factor		Overall	Installation	Pressure		Width	Sprinkler
				US	Metric	Length (in)	Position	(psi)	Angle	(ft)	Identification Number (SIN)
		5/8	3/4	9.8	141	2 <sup>5</sup> /8	Upright	7	139	28	R0426
								52	141	44	
	Cornice							100	141	44	
	(Model FM)	1/2	1/2	6.5	94	2 <sup>5</sup> /8	Upright	7	136	20	
								52	138	44	R0428
								100	140	44	

For specific water distribution information, refer to the spray distribution section of the catalog.

The equipment presented in this bulletin is to be installed in accordance with the latest published Standards of the National Fire Protection Association, Factory Mutual Research Corporation, or other similar organizations and also with the provisions of governmental codes or ordinances whenever applicable. Products manufactured and distributed by Reliable have been protecting life and property for over 80 years, and are installed and serviced by the most highly qualified and reputable sprinkler contractors located throughout the United States, Canada and foreign countries.

Manufactured by



Reliable Automatic Sprinkler Co., Inc.

(800) 431-1588 Sales Offices (800) 848-6051 Sales Fax (914) 829-2042 Corporate Offices www.reliablesprinkler.com Internet Address



Recycled Paper