

Installations are a breeze with the RFC's deeper cup

Hydraulic options: Widest selection of flat plate residential pendent K-factors in the industry: 3.0 (43), 4.3 (62), 4.9 (71), 5.8 (84), 7.6 (109).

Fast installation and uninterrupted protection:

Wrenchable cap stays in place before, during, and after installation - until the cover plate is installed.

Safe and clean installation:

Smooth-edged, durable pushon/thread-off cover plate in a variety finishes to complement any decor.

Dedicated emergency wrench: Economical reinforced plastic wrench available for the spare sprinkler cabinet.



Install without removing the protective cap with Model W3



Reinforced plastic Model W8 for spare sprinkler cabinet.

Robust stainless steel metal wrench available for repeated use.

Worried about glass bulbs? Model RFC Series Sprinklers employ a rugged fusible link operating element; each link is 100% x-ray validated.





Align the indicator with finished ceiling. Caps are color coded per temp rating.

Over one hundred years of quality manufacturing: Designed and assembled by Reliable® in Liberty, South Carolina, USA.



COVER PLATE FINISHES



Standard Finish

Chrome Plated

White Paint

Standard Woodgrain Finish



White Wash



Silver Birch



Beige Birch

Special Application Finish



Satin Chrome

Stainless Steel Clad

Golden Pine



Red Oak



Warm Maple



Red Cherry



Dark Walnut



Espresso



Rustic Beige



Weathered Grey



© 2021 Reliable Automatic Sprir

Slate Grey

Custom Paint & Prints



The only limit is your imagination!

See Bulletin 203 for details. Printed Finishes' hue shown may vary due to print and screen variation.



reliablesprinkler.com/covers