

THE FIRST OF ITS KIND MODEL G5-80F

New Reliable Sprinkler. Same Reliable Quality.

- *The only K8.0 (115 metric) Flat Plate Concealed Sprinkler that is FM approved.*
- *Standard response, standard coverage.*
- *Available with standard finish or stainless steel clad cover plate, with or without gasket.*
- *3/4" (19mm) cover plate adjustment.*
- *Available in 165°F (74°C) or 212°F (100°C) temperature rating.*
- *See bulletin 034 for more information.*

Reliable[®]

reliablesprinkler.com

