

Concealed, Horizontal Sidewall Quick Response Sprinklers

G6-80 HSW QR EC, (K-8.0)

- With Listed Spacing up to 16' x 24' (4.9m x 7.3m)
- UL Listed as QR EC for Light Hazard Applications
- Rated to 175 psi (12.0 bar)
- Push-on/pull-off flat cover plate solid or perforated
- 1/4" (6.3 mm) cover plate adjustment
- 3/4" NPT (R3/4) Male Thread
- SIN RA4762, Bulletin 047





G6-56 HSW QR, (K-5.6)

- For installation in accordance with NFPA13
- UL Listed as QR, Standard Coverage for Light and Ordinary Hazard Applications
- Rated to 175 psi (12.0 bar)
- Push-on/pull-off flat cover plate solid or perforated
- 1/4" (6.3 mm) cover plate adjustment
- 1/2" NPT (R1/2) Thread
- SIN RA5035, <u>Bulletin 050</u>



