

| Description | Part Number | List Price |
|---|-------------|--------------|
| MODEL E1 — RETARD CHAMBER | | |
| Coupling Restriction & Drain | 92096521 | C\$ 179.87 |
| Cast Iron Ell 3/4" | 98164400 | C\$ 90.80 |
| Nipple, 3/4" x 1-1/2" | 98523203 | C\$ 26.00 |
| Orifice Restriction | 98580001 | C\$ 124.21 |
| Orifice Restriction, Drain | 98580002 | C\$ 112.86 |
| MODEL C — MECHANICAL SPRINKLER ALARM | | |
| Gong | 93806612 | C\$ 1,034.01 |
| Cover Gasket | 93706602 | C\$ 90.80 |
| Gong Belt | 91106601 | C\$ 63.31 |
| Wall Plate | 95106602 | C\$ 652.47 |
| Body Cover | 92106603 | C\$ 224.84 |
| Aluminum Cast Body | 91006602 | C\$ 371.07 |
| Wall Support Washer | 96906603 | C\$ 124.21 |
| Clean Out Plug | 98604402 | C\$ 4.60 |
| Pelton Wheel | 97006603 | C\$ 213.49 |
| Bearing - Need to order 2 | 90506603 | C\$ 26.00 |
| Drive Shaft | 96206603 | C\$ 106.00 |
| Drive Shaft Adaptor | 90086601 | C\$ 134.91 |
| Body Assembly1 | 73020043 | C\$ 2,582.95 |
| Striker Assembly2 | 73020063 | C\$ 472.61 |
| Gong Assembly3 | 73020093 | C\$ 2,021.53 |
| Mechanical Sprinkler Alarm Gong | 93806603 | C\$ 2,582.95 |
| Phenolic Striker | 96456601 | C\$ 79.46 |

1 Contains:

Bearing, Body, Body Cover, Cover Gasket, Cover Screws (5), Pelton Wheel, Plug 1/2"

2 Contains:

Striker Arm, Striker Bushing, Rivet, Striker

| Description | Part Number | List Price |
|---|-------------|--------------|
| MODEL D — 4" DRY PIPE VALVE | | |
| Cover | 92116224 | C\$ 1,178.76 |
| Cover Bolts - Need to order 7 | 91106124 | C\$ 8.30 |
| Clamping Ring | 95306224 | C\$ 898.44 |
| Clamping Ring Screw - Need to order 6 | 95606224 | C\$ 49.77 |
| Clapper Latch | 94446223 | C\$ 427.63 |
| Clapper Latch Pin | 95016224 | C\$ 179.87 |
| Clapper Latch Spring | 96406224 | C\$ 79.46 |
| Seat (Note: Seat wrench required. see Price Book page S-185) | 96016224 | C\$ 2,920.63 |
| Seat "O" Ring | 95446224 | C\$ 74.00 |
| Body "O" Ring | 95436224 | C\$ 134.91 |
| Hinge Pin | 95006224 | C\$ 281.37 |
| Bushing - Need to order 2 | 91406224 | C\$ 57.43 |
| Cover Gasket | 93706224 | C\$ 258.46 |
| Clapper Rubber Facing | 93406224 | C\$ 922.01 |
| Clapper Assembly -Clapper Rubber Facing, Clamping Ring & Clamping Ring Screws | 71010424 | C\$ 5,502.72 |

| Description | Part Number | List Price |
|--|-------------|--------------|
| MODEL D — 6" DRY PIPE VALVE | | |
| Cover | 92116226 | C\$ 2,470.30 |
| Cover Bolts - Need to order 8 | 91106126 | C\$ 13.31 |
| Clamping Ring | 95306226 | C\$ 1,056.04 |
| Clamping Ring Screw - Need to order 8 | 95606224 | C\$ 49.77 |
| Clapper Latch | 94446223 | C\$ 427.63 |
| Clapper Latch Pin | 95016224 | C\$ 179.87 |
| Clapper Latch Spring | 96406224 | C\$ 79.46 |
| Seat (Note: Seat wrench required, see Price Book page S-185) | 96016226 | C\$ 4,267.68 |
| Seat "O" Ring | 95446226 | C\$ 112.86 |
| Body "O" Ring | 95436226 | C\$ 134.91 |
| Hinge Pin | 95006226 | C\$ 382.67 |
| Bushing (2) | 91406224 | C\$ 57.43 |
| Cover Gasket | 93706226 | C\$ 269.80 |
| Clapper Rubber Facing | 93406226 | C\$ 1,034.01 |
| Clapper Assembly - Clapper Rubber Facing, Clamping Ring & Clamping Ring Screws | 71010624 | C\$ 7,411.15 |
| MODEL D1 & D — DRY PIPE VALVE TRIMMINGS | | |
| Drip Cup, Support Clip, Bolt1 | 71010471 | C\$ 494.64 |
| Clip Support 1" | 98084400 | C\$ 22.27 |
| Clip Support Screw | 98084401 | C\$ 10.06 |
| Bolt & Nut | 91106911 | C\$ 10.06 |
| Priming Chamber 1/2" | 71010432 | C\$ 1,145.98 |
| Priming Cup / Fill Cup 1/2" | 75000050 | C\$ 242.51 |
| Strainer 3/4" | 78650200 | C\$ 470.19 |
| Ball Drip Valve 1/2" Mech. Mod. C | 78653100 | C\$ 800.03 |
| Ell, Brass, Male Comp. 3/16" x 1/4" | 98164406 | C\$ 134.91 |
| Connector, Brass, Male Comp2 | 98085630 | C\$ 79.46 |
| Copper Tubing 1/4" x 18" - Need to order 2 | 98768000 | C\$ 124.21 |
| Copper Tubing 3/15" x 42" | 98768001 | C\$ 53.00 |
| Copper Tubing 1/4" x 48" | 98768002 | C\$ 179.87 |

| Description | Part Number | List Price |
|---|-------------|--------------|
| MODEL D — DRY PIPE VALVE TRIMMINGS | | |
| Air Pressure Gauge | 98248000 | C\$ 201.90 |
| Water Pressure Gauge | 98248001 | C\$ 188.83 |
| Ball Valve 1/2" | 98840105 | C\$ 461.03 |
| Angle Valve 2" | 98840100 | C\$ 797.83 |
| Angle Valve 1/4" Mod. B2 | 98840101 | C\$ 224.84 |
| 1/4" 3 Way Bronze Gauge Valve - Need to order 2 | 98840160 | C\$ 336.83 |
| Globe Valve 3/4" | 98840170 | C\$ 461.03 |
| Globe Valve 1/2" | 98840171 | C\$ 404.71 |
| Horizontal Check Valve 3/4" | 98840180 | C\$ 550.30 |
| Horizontal Check Valve 1/2" | 98840181 | C\$ 442.70 |
| Relief Valve Bronze 1/2" | | C\$ Call |
| MODEL B1 — ACCELERATOR | | |
| Body Push Rod Guide Sub. Assembly | 91007000 | C\$ 1,459.87 |
| Top Chamber Cover | 92106411 | C\$ 1,796.70 |
| Drain Plug 1/4" - Need to order 2 | 98604413 | C\$ 124.21 |
| Top Chamber Bolt - Need to order 6 | 91106311 | C\$ 79.46 |
| Sensing Diaphragm | 92206311 | C\$ 169.39 |
| Diaphragm Retainer | 95276321 | C\$ 90.80 |
| Diaphragm Washer - Need to order 2 | 96906311 | C\$ 67.90 |
| Diaphragm Spring | 96406311 | C\$ 79.46 |
| Push Rod Guide | 93906312 | C\$ 112.86 |
| Push Rod Guide "O" Ring | 95406315 | C\$ 112.86 |
| Accelo Check "O" Ring - Need to order 2 | 95406311 | C\$ 67.90 |
| Poppet Spring | 96406314 | C\$ 90.80 |
| Poppet | 95226321 | C\$ 90.80 |
| Poppet "O" Ring | 95406313 | C\$ 79.46 |
| Accelo Check Nut | 94906327 | C\$ 79.46 |
| Accelo Check Screws - Need to order 4 | 95606311 | C\$ 57.43 |
| Accelo Check Spring | 96406317 | C\$ 79.46 |
| Accelo Check Poppet | 95226327 | C\$ 124.21 |
| Accelo Check Diaphragm | 92206317 | C\$ 79.46 |
| Accelo Check Washer | 96906327 | C\$ 57.43 |
| Valve Plug "O" Ring | 95406312 | C\$ 79.46 |
| Diaphragm Nuts - Need to order 2 | 94906321 | C\$ 101.50 |
| Valve Plug Assembly ¹ | 73016333 | C\$ 246.89 |
| Filter Assembly ² | 73016343 | C\$ 382.67 |

¹ Contains:

Valve Plug, Valve Plug Pin

² Contains:

Filter, Filter Retainer