

SPRINKLERS**Standard Spray QR - Quick Response**

- S-1 F1FR - Upright
- S-3 F1FR-300 - Upright
- S-4 F1FR - Pendant, Recessed
- S-6 F1FR-300 - Pendant, Recessed
- S-7 F1FR - Horizontal Sidewall
- S-8 F1FR56-300 - HSW, Rec HSW and SWC56 Concealed
- S-9 F1FR - Vertical Sidewall
- S-10 F1FR - Conventional
- S-11 F1FR-SS Stainless Steel - Upright and Pendant
- S-12 F1FR LL - Pendant and CCP
- S-13 KFR56 - Upright and Pendant
- S-14 KFR56-300 - Upright & Pendant
- S-15 KFR56-300 - HSW and CCP
- S-16 KFR56 HSW and CCP
- S-17 KFR80 Upright and Pendant
- S-18 GFR Upright
- S-19 GFR - Pendant & HSW
- S-20 G5-80, G5-56, G5-42 & G5-28
- S-21 G6-56 HSW QR
- S-22 G5-80, G5-56, G5-42 and G5-28 QR "Sealing" Concealed
- S-23 G5-56 300 QR "Sealing" Concealed
- S-24 G5-56 300 Concealer
- S-25 F1FR CCP and F1FR-300 CCP
- S-26 XL Commercial - Pendant and HSW

Standard Spray SR - Standard Response

- S-27 F1 - Upright
- S-29 F1-SS Stainless Steel - Upright & Pendant
- S-30 F1-300 - Upright
- S-31 F1 - Pendant, Recessed
- S-33 F1-300 - Pendant, Recessed
- S-34 F1 - Conventional
- S-35 F1 - Horizontal Sidewall
- S-36 F1 - Vertical Sidewall
- S-37 G - Upright
- S-39 G - Pendant
- S-41 G - Conventional
- S-42 G - Vertical Sidewall
- S-43 G - Horizontal Sidewall, Recessed
- S-45 G - Recessed
- S-47 G4
- S-48 G4-11
- S-49 G4-300 - Concealed
- S-51 G5-80, G5-56, G5-42 and G5-28 SR "Sealing" Concealed
- S-52 G5-56 300 SR "Sealing" Concealed

Extended Coverage

- S-53 G6-80 HSW QR EC
- S-54 JL112 and J112 - Upright, Pendant and Rec Pendant
- S-55 F1FR56 QREC and F1FR EC - Pendant, Recessed
- S-56 F1FR 56-300 and F1FR-300 QREC - Pendant, Recessed
- S-57 F1FR 56-300 and F1FR-300 QREC EC9 - HSW, Recessed
- S-58 F1FR 56 EC8 and F1FR QREC EC9 - HSW, Recessed
- S-59 F1FR 56-300 and F1FR-300 QREC CCP - Concealed
- S-60 DH56 - HSW, HSW Recessed, HSW Concealed
- S-61 DH80 - HSW, HSW Recessed, HSW Concealed
- S-62 G4 XLO-QR ECLH/ECOH
- S-62 KFR-CCS Combustible Concealed Space
- S-63 SWC Concealed Sidewall
- S-64 F1 56 SREC and F1 EC - Pendant

- S-65 F1 56-300 SREC and F1-300 EC - Pendant, Recessed
- S-66 G - EC4 - HSW
- S-66 GFR VELO ECOH - Upright
- S-66 GFR VELO ECOH - Pendant, Recessed
- S-67 MBEC-14- HSW

Residential

- S-68 F1RES 30, KRES 30 - Pendant, Rec Pendant, CCP
- S-69 F1RES 49 & KRES49 - Pendant, Rec Pendant, CCP
- S-70 F1RES 44, KRES 44- HSW, REC HSW, SWC44
- S-71 F1RES 58, KRES 58 - Pendant, Rec Pendant, CCP, HSW
- S-72 F1RES 58 HSWX & KRES 58 HSWX
- S-73 F1RES 76 - Pendant, Rec Pendant, CCP
- S-74 RFC43 Flat Concealed
- S-74 RFC30 Flat Concealed
- S-74 RFC49 Flat Concealed
- S-74 RFC58 Flat Concealed
- S-74 RFC76 Flat Concealed
- S-75 RFC49plus Flat Concealed
- S-76 RFS42 Flat Plate Concealed HSW
- S-77 F3RES44 Dry HSW
- S-78 F3RES44 Dry Recessed HSW/F2
- S-79 F3RES44 Dry HSW/HB
- S-80 F1RES 30 LL - Pendant, Rec Pendant, CCP
- S-81 F1RES 49 LL - Pendant, Rec Pendant, CCP
- S-82 F1RES 44 LL - HSW, Rec HSW, SWC
- S-83 F1RES 58 LL - Pendant, Rec Pendant, CCP, HSW
- S-84 RFC30 LL Flat Concealed
- S-84 RFC43 LL Flat Concealed
- S-84 RFC49 LL Flat Concealed

Storage

- S-85 JL14 ESFR
- S-85 JL17 ESFR
- S-86 P22 ESFR
- S-86 P25 ESFR
- S-87 N28 ESFR
- S-88 GXLO Upright and Pendant
- S-88 GXLO Intermediate
- S-89 J168 - Upright
- S-89 N252 EC - Pendant and Recessed Pendant
- S-90 LB11 HSW
- S-91 GL112 Upright and Pendant
- S-91 G VELO Pendant
- S-92 GSR112 Upright and Pendant
- S-93 GQR112 Upright and Pendant
- S-94 F1FR 56 & F1FR Intermediate - Upright and Pendant
- S-95 F1 56 & F1 Intermediate - Upright and Pendant
- S-96 KFR56 Intermediate - Upright and Pendant
- S-97 Intermediate Level Sprinkler with D-3 and D-5 Guard Assembly
- S-99 GFR Intermediate - Upright and Pendant
- S-100 G Intermediate Level - with D-3 and D-5 Guards/Shields
- S-103 D-1 - Int. Level Sprinkler and Guard Assembly

Special

- S-105 Attic Sprinklers
- S-106 LT56 Series Pendant
- S-107 LT56 Series CCP
- S-108 LT56C Flat Concealed
- S-109 XL INST - Institutional
- S-110 F4FR-NF
- S-110 KFR CCS Combustible Concealed
- S-111 WP56 & WP56L Window Sprinklers

Dry

- S-113 F3QR56-Upright
- S-114 F3QR56 - Pendent
- S-116 F3QR56 - Pendent / HB
- S-118 F3QR56 - Recessed Pendent /FP
- S-120 F3QR56 - Recessed Pendent / F1
- S-122 F3QR56 - Horizontal Sidewall
- S-124 F3QR56 - Horizontal Sidewall / HB
- S-126 F3QR56 - Recessed Horizontal Sidewall / FP
- S-128 F3QR56 - Recessed Horizontal Sidewall / F1
- S-130 F3QR56 - Concealed
- S-132 F3QR80 - Pendent
- S-133 F3QR80 - Pendent / HB
- S-134 F3QR80 - Recessed Pendent / FP
- S-135 F3QR80 - Horizontal Sidewall
- S-136 F3QR80 - Horizontal Sidewall / HB
- S-137 F3QR80 - Horizontal Sidewall / FP
- S-138 F3QR80 - Concealed
- S-139 G5-56 Dry
- S-140 DH56 Dry - Horizontal Sidewall
- S-141 DH56 Dry - Horizontal Sidewall / HB
- S-142 DH56 Dry - Recessed Horizontal Sidewall
- S-143 DH56 Dry - Concealed
- S-144 DH80 Dry - Horizontal Sidewall
- S-145 DH80 Dry - Horizontal Sidewall / HB
- S-146 DH80 Dry - Recessed Horizontal Sidewall
- S-147 DH80 Dry - Concealed
- S-148 F3-56 Upright
- S-149 F3-56 - Pendent
- S-151 F3-56 - Pendent / HB
- S-153 F3-56 - Recessed Pendent / FP
- S-155 F3-56 - Recessed Pendent / F1
- S-157 F3-56 - Horizontal Sidewall
- S-159 F3-56 - Horizontal Sidewall / HB
- S-161 F3-56 - Recessed Horizontal Sidewall / FP
- S-163 F3-56 - Recessed Horizontal Sidewall / F1
- S-165 F3-56 - Concealed
- S-167 F3-80 - Pendent
- S-168 F3-80 - Pendent / HB
- S-169 F3-80 - Recessed Pendent / FP
- S-170 F3-80 - Horizontal Sidewall
- S-171 F3-80 - Horizontal Sidewall / HB
- S-172 F3-80 - Horizontal Sidewall / FP
- S-173 F3-80 - Concealed

Nozzles

- S-174 TNL280 Pendent Spray Nozzle
- S-175 B & FM - Spray Nozzles - Window & Cornice Types
- S-176 F1-FTR - Pilot Line Detector (PLD)
- S-176 HV - High Velocity Nozzles

Multipurpose Residential Risers and Accessories

- S-181 Accessories - Cabinets & Escutcheons
- S-183 Accessories - Multipurpose LL Residential Riser
- S-183 Accessories - Gauges, Connections, Drips, Misc.
- S-184 Accessories - Electrical Components

Accessories**Escutcheons**

- S-185 FP Push-On / Thread Off Escutcheons
- S-185 G/F1 Escutcheon and Collar Assembly
- S-185 G/F1 Escutcheon Only
- S-185 G/F1 Collar Only
- S-185 G/F1 and G/F2 Escutcheon Extender Ring
- S-185 G/F2 Escutcheon & Collar Assembly

- S-185 G/F2 Escutcheon Only
- S-185 G/F2 Collar Only
- S-186 B, C & HB Two Sprinkler Escutcheons
- S-186 Sure-Off Tester

Spk Guards/Emergency Cabinets

- S-187 Sprinkler Guards & Shields
- S-187 Emergency Cabinets
- S-189 For Sprinklers Wrenches

Printed Coverplates

- S-190 Models G6, G5, RFS42

Replacement Coverplates

- S-191 G1 Concealed Replacement Coverplates

Special Services

- S-192 Special Services / Special Finishes

VALVES**Alarm And Check Valves**

- V-1 E and E3 Alarm Valves - FxF, FxG, GxG
- V-2 E3 - Trim Segmented & Loose
- V-3 Miscellaneous Alarm Valve Trim
- V-3 Retard Chamber and Mechanical Spk. Alarm
- V-3 Valve Seat Wrenches
- V-3 G - Riser Check - 2½", 3", 4", 6"
- V-3 G - Grooved Check - 2½", 3", 4", 6"
- V-3 CVE - Swing Check - 4", 6", 165mm, 8"

Deluge Valves

- V-4 DDV Deluge Valves - Electric Trim
- V-5 DDV Deluge Valves - Wet Pilot Line Trim
- V-6 DDV Deluge Valves - Dry Pilot Line Trim
- V-7 DDV Deluge Valves-Remote Reset
- V-8 DDV Deluge Valves-Remote Reset Pressure Regulating
- V-9 DDV Deluge Valves-Dry Pilot Pressure Regulating
- V-10 DDV Drain Trims & Accessories
- V-11 DDX Deluge Valves & Trim
- V-11 DDX Deluge Valves-Electric,Wet Pilot, Dry Pilot-Fully Assembled

Pressure Control Valves

- V-13 PRV Diaphragm Pressure Regulating Valves

Low Pressure Dry Systems

- V-14 DDX-LP Dry Pipe Valve Systems

Dry Pipe Valves

- V-15 FX- 2",2 1/2",3" 4",6" Valve and Trim
- V-16 FX- 2",2 1/2",3" 4",6" Fully Assembled

Control Valves

- V-17 PIV, OSY Gate Valves & Bronze Butterfly Valves
- V-19 Supervised Butterfly Valves

Accessories

- V-20 ACD Dry Systems Auxiliary
- V-20 B-1 – Accelerator, A-2 Air Maintenance Device, B-1 Air Maintenance Device
- V-21 Electronic Accelerators
- V-21 Test and Drain, Pressure Relief Valves, AAV Auto Air Vent
- V-22 Air Compressors
- V-28 Pressure Gauges
- V-28 Inspectors Test Connections
- V-28 Automatic Ball Drips
- V-28 Mechanical Ball Drips
- V-28 Strainers (Misc. Items)
- V-28 Sprinkler/Valve System Signs
- V-29 Residential Riser
- V-30 CR2 Commercial Riser
- V-32 FCA2 Floor Control Valves

SPECIAL HAZARDS/SPECIAL SYSTEMS**Model H Deluge, Preaction, PrePak 1 1/2"**

- SS-1 Model H Deluge / Riser Assemblies and Trim

Single, Double, Interlock

- SS-2 DDX Single Interlock - Fully Assembled
- SS-3 DDX Double Interlock - Fully Assembled
- SS-4 DDX Preaction Trim

PrePaK

- SS-5 DDX Type D PrePaK
- SS-6 DDX Type F PrePaK
- SS-7 DDX Electric Release PrePaK
- SS-8 DDX Wet Pilot PrePaK
- SS-9 DDX Dry Pilot PrePaK
- SS-10 DDX-LP PrePaK System
- SS-11 DDX N2 Blast PrePaK Systems

Accessories

- SS-12 Accelerator
- SS-12 Pull Boxes
- SS-12 RPC 4410 RC Control Panel
- SS-12 System Modules / Batteries
- SS-13 Electric Alarm Bells, Supervisory Air Supply, Valve Seat Wrenches
- SS-13 LPC Components
- Protectowire

SYSTEM COMPONENTS**Grooved Couplings And Fittings - Reliable**

- SC-1 Couplings | Rigid, Flexible, Reducing
- SC-4 Elbows | 90, 22.5, 11.25
- SC-6 Tees | standard, short radius, u-bolt, mech-threaded/grooved, reducing
- SC-11 Fittings | end of run, flanges, caps

Grooved Couplings And Fittings - Titus

- SC-15 Couplings | grooved kwik rigid, flush flex

Grooved Couplings And Fittings - Anvil

- SC-16 Couplings, Lightweight and Rigid
- SC-16 Couplings, Standard and Reducing
- SC-16 Couplings, Standard and Rigid w/Flush Seal

- SC-16 90° Elbows
- SC-16 45° Elbows
- SC-16 Tees
- SC-16 Flanges, Short Radius 90° Elbows
- SC-16 Short Radius 45° Elbows and Tees
- SC-16 Concentric Reducers, Caps
- SC-16 Caps (cont'd), Star-let Tees (MT3)
- SC-16 Mechanical Tees
- SC-16 Mechanical Tee-Cross (Threaded)
- SC-16 Mechanical Tee-Cross (Grooved), Replacement Gaskets
- SC-16 End of Run Fittings (SE-5)
- SC-16 Couplings, Lightweight and Rigid
- SC-18 Couplings, Lightweight and Rigid w/Flush Gasket
- SC-19 Couplings, Reducing
- SC-20 45° Elbows and 90° Elbows
- SC-21 Fire Rite 90° Elbows and Standard Tees
- SC-22 Fire Rite Tees & Concentric Reducers (GxG)
- SC-24 Concentric Reducers (GxT)
- SC-26 Caps, Gruvlok Flanges
- SC-27 Clamp-T (Grooved Outlet)
- SC-28 Clamp-T (Female Threaded Outlet)
- SC-30 Steel Cross
- SC-31 Replacement Gaskets
- SC-32 Sock-lts, 90° Straight and Reducing, Tees

US Made Cast Iron Fittings

- SC-34 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-36 Reducing Tees
- SC-37 Bullhead Tees, Crosses, Plugs, Caps (malleable), Couplings (malleable), Unions (malleable)
- SC-38 Hex Bushings, Companion Flanges, Pipe Dope, Teflon Tape, Cutting Oil
- SC-39 90° Elbows, Reducing 90° Elbows, 45° Elbows Reducing Couplings, Standard Tees
- SC-40 Reducing Tees, Couplings, Caps, Unions
- SC-42 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-42 Reducing Tees
- SC-42 Bullhead Tees, Crosses, Caps, Couplings
- SC-42 Bullhead Tees, Crosses (Standard & Reduc.) Plugs, Pipe Dope, Teflon Tape

Cast Iron & Ductile Fittings - Foreign Anvil

- SC-42 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-45 Reducing Tees
- SC-46 Bullhead Tees, Crosses, Caps, Couplings Pipe Dope, Teflon Tape, Cutting Oil
- SC-48 Bullhead Tees, Crosses (Standard & Reduc.) Plugs, Pipe Dope, Teflon Tape, Cutting Oil
- SC-49
- SC-49

US Made Flanged Fittings

- SC-49 Flanged Elbows, Reducing
- SC-50 Flange Tees
- SC-51 Flanged Reducers
- SC-52 Companion, Reducing Flange

Expansion Loops

- SC-53 Threaded & Grooved Models

CPVC Pipe, Fittings, & Hangers

- SC-55 Pipe, Anti-Freeze
- SC-56 Hangers (Single, Double, Sidemount, Stand-Off)
- SC-57 Sealant, Caulk
- SC-58 Elbows, Head Adapters, Standard Tees, Tees (Reduc. and Run Reduc.), Tee Head
- SC-59 Adapters Tee Head Adapters (cont'd), Bushings,
- SC-61 Head Adapters, Adapters, Couplings, Reduc. Couplings
- SC-62 Grooved Adapters, Caps, Crosses, Cement, Thread Sealant
- SC-63 Torque Safe Fittings

Tee-lets

- SC-64 Tee-lets
- SC-66 Grooved Shape Nipples - Sch 40
- SC-67 Grooved Shape Nipples - Sch 10
- SC-68 Import Olets
- SC-69 Welded Outlets

Hangers

- SC-73 Ring Hangers, Beam Clamps, Riser Clamps, Wall Plates
- SC-74 Earthquake Bracing
- SC-75 Eye Sockets, All Thread Rod, Hex Nuts, Washers, Drop Anchors

Super Screws

- SC-76 Sammy Super Screws

Fire Department Equipment

- SC-78 Fire Department Connections, Hose Valves, Accessories

Nipples

- SC-81 Adjustable Wet Drop Nipples (M x F, M x M)
- SC-82 Steel Nipples, Blck & Galvanized

Valves

- SC-87 Riser Check, Grooved Check, Swing Check, Flanged Check, Gasket Kits
- SC-89 OS&Y, PIV, Butterfly Valves (GxG and Wafer)
- SC-90 Reliable PIV, OSY Gate & Bronze Butterfly Valves
- SC-92 Reliable Butterfly Valves
- SC-93 Butterball Valves (Threaded and Grooved)
- SC-94 Foreign Trim Valves - Globe, Ck, 3-way Angle
- SC-95 Valves, FDC, and Accessories
- SC-98 US Made Trim Valves - Globe, Ck, 3-way, Angle
- SC-100 Detector Check, In-Building Riser, Wafer Check, Test & Drains

Backflows

- SC-103 2000ss, 2001ss, 3000ss, 30001ss
- SC-104 4000ss, 4001ss, 5000ss, 5001ss
- SC-105 Colt Series: C-200 OS&Y, C-200 BFV, C-300 OS&Y, C-300 BFV
- SC-106 Colt Series: C-400 OS&Y, C-400 N or Z, C-500 OS&Y, C-500 N or Z
- SC-107 Maxim Series: M-200 OS&Y, M-200 BFV, M-300 OS&Y, M-300 BFV
- SC-108 Maxim Series: M-400 OS&Y, M-400 N or Z, M-500 OS&Y, M-500 N or Z
- SC-109 Deringer
- SC-111 OS & Y

Air Compressors

- SC-116 Bare, with Check, Tank Mounted

Electrical Equipment

- SC-124 Waterflow Detector, Tamper Switches, Electric Bells, Accessories
- SC-126 Canadian versions

Flexible Drops

- SC-127 Flexible Drops

Residential Fire Pumps & Accessories

- SC-129 Residential Fire Pumps, Tanks, Kits

Elmdor Access Doors & Equipment

- SC-130 Elmdor Access Doors & Equipment

Steel Pipe

- SC-136 Schedule 40 & 10, Flowpipe, Threadable Lightwall, and Special Requests

Expansion Tanks

- SC-137 Expansion Tanks

REPLACEMENT PARTS**Valve Service Kits & Valve Seat Wrenches**

- RP-1 Model A Dry Pipe Valve
- RP-1 Model D Dry Pipe Valve
- RP-2 Model EX Dry Pipe Valve
- RP-3 Model FX Dry Pipe Valve
- RP-4 DDX Valve With Stainless Steel Clapper
- RP-5 Early Gen DDX Valves with Brass Clapper
- RP-6 Model E3 (Small) Alarm Valve
- RP-6 Model E (Large) Alarm Valve / CVE Check Valve

Alarm Valves

- RP-7 Alarm Valves & Trimmings

Dry Pipe Valves

- RP-11 Dry Pipe Valves and Trimmings
- RP-14 Accelerator

Deluge Valves

- RP-15 Deluge Valves and Trimmings
- RP-22 External Reset Device
- RP-22 Air Maintenance Devices

Miscellaneous

- RP-23 Sight Test Connection
- RP-24 Sight Drain, Emergency Pull Box, Copper Tubing, Parts for Model B Air Compressor Panel
- RP-25 Air Compressor