

Description	Part Number	List Price
MODEL A — 2 1/2" DELUGE VALVE		
Socket Flat Head Screw - Need to order 6	95616402	C\$ 49.77
Socket Head Cap Screw - Need to order 8	95606402	C\$ 49.77
Rubber Facing	92206402	C\$ 640.89
Clamping Ring	95306402	C\$ 809.18
Rubber Seal	93406402	C\$ 191.44
Cover Bolts - Need to order 8	91106123	C\$ 9.39
MODEL B — 4" DELUGE VALVE		
Cover Gasket	93706404	C\$ 224.84
Cover Bolts -Need to order 6	91106404	C\$ 11.34
Seat "O" Ring	95406404	C\$ 28.36
Clapper Clamping Ring		C\$ Call
Clapper Rubber Facing	93406404	C\$ 853.48
Clamping Ring Screws -Need to order 4	95606404	C\$ 57.43
Drain Plug	98604403	C\$ 57.43
"E" Ring, Pin Lever - Need to order 2	95316408	C\$ 124.21
Lever Shaft	96216404	C\$ 394.00
Lever Shaft Model BX	96216424	C\$ 281.37
"O" Ring, Push Rod	95406406	C\$ 45.84
"O" Ring, Push Rod	95406407	C\$ 46.09
"O" Ring, Push Rod Guide	95406408	C\$ 79.46
Push Rod Spring	96406406	C\$ 394.00
Push Rod Cover Gasket	93716406	C\$ 57.43

Important Note:

Above parts are 1241 and subsequent, 1240 and prior requires replacements part kit

Description	Part Number	List Price
MODEL B — 4" DELUGE VALVE		
Push Rod Cover Assembly ¹	71040419	C\$ 1,459.87
MODEL B — 6" DELUGE VALVE		
Cover Gasket	93706406	C\$ 246.89
Cover	92106406	C\$ 1,459.87
Cover Bolts - Need to order 8	91106406	C\$ 11.34
Push Rod Cover		C\$ Call
Seat "O" Ring	95436126	C\$ 28.60
Clapper Clamping Ring	95306406	C\$ 427.63
Clapper Shaft	96206406	C\$ 427.63
Clapper Rubber Facing	93406406	C\$ 876.18
Clamper Ring Screws - Need to order 4	95606406	C\$ 67.90
"E" Ring, Pin Lever - Need to order 2	95316407	C\$ 224.84
Lever Shaft	96216406	C\$ 427.63
"O" Ring, Push Rod	95406406	C\$ 45.84
"O" Ring, Push Rod	95406407	C\$ 46.09
"O" Ring, Push Rod Guide	95406408	C\$ 79.46
Push Rod Cover Gasket	93716406	C\$ 57.43
Drain Plug	98604403	C\$ 57.43
Push Rod Spring	96406406	C\$ 394.00
Push Rod Cover Assembly ¹	71040419	C\$ 1,459.87

¹ Contains:

Push Rod Cover, Inlet Orifice

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit

Description	Part Number	List Price
MODEL DDX — 2", 2-1/2" & 3" DELUGE VALVES		
Cover, Pushrod, Assembly	71040416	C\$ 1,351.84
Clapper Assembly	71041300	C\$ 4,492.48
Screw, Hex Cap. 1/2-13 x 1-1/4", ZN PLTD, Grade A	91106123	C\$ 9.39
Mounting Ring, Machined	91306013	C\$ 343.80
Seal Assembly	93416003	C\$ 191.44
Gasket, Access Cover	93706003	C\$ 208.47
Pushrod, Guide	93916006	C\$ 193.19
Knob, Reset, Assembly	94356007	C\$ 219.16
Piston, Machined	95106006	C\$ 1,326.07
Diaphragm	95276006	C\$ 136.01
Clip, Retaining, 3/8" Shaft	95306268	C\$ 21.81
O-Ring - Need to order 114	95406007	C\$ 46.09
O-Ring - Need to order 912	95406024	C\$ 46.09
O-Ring - Need to order 014	95406407	C\$ 46.09
O-Ring - Need to order 150	95406410	C\$ 46.09
O-Ring - Need to order 147	95406411	C\$ 46.09
Screw, Socket Head, 1/4"-20 x 5/8"	95606114	C\$ 49.99
Screw, Cap. #6-32 x 1/2", SS	95606133	C\$ 49.99
Seat Machined	96016003	C\$ 1,289.87
Pin. Hinge	96206003	C\$ 182.27
Pin. Lever	96216003	C\$ 731.04
Spacer, Clapper Pin	96310003	C\$ 182.27
Spring, Lever	96406003	C\$ 98.46
Spring, DDX	96406906	C\$ 109.37
Washer, Lock, # 6, SS	96906112	C\$ 5.23

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit



Description	Part Number	List Price
DDV REPLACEMENT PARTS		
ASSY,DIAPHRAGM,DDV,2 1/2&3	95277630	C\$ 769.96
ASSY,DIAPHRAGM,DDV,4	95277640	C\$ 1,539.93
ASSY,DIAPHRAGM,DDV,6	95277660	C\$ 3,272.33
SCR,HEX,1/2-13X1,ZINC	95606179	C\$ 9.74
SCR,HEX,5/8-11X1,ZINC	95606182	C\$ 9.74
SCR,HEX,7/8-9X1-1 1/2,ZINC	95606180	C\$ 12.99
STUD,7/8-9X3,ZINC	96506604	C\$ 15.39
NUT,HEX,7/8"-9	94906924	C\$ 7.79

Description	Part Number	List Price
MODEL DDX — 4", & 6", DELUGE VALVES		
Cover, Pushrod, Assembly	71040416	C\$ 1,351.84
Seat, 4"	96016004	C\$ 1,337.90
Clapper Assy, 4" DDX	71041401	C\$ 5,959.14
Cover, 4"	92116064	C\$ 1,143.83
Gasket, Cover, 4"	93706004	C\$ 208.47
Lever, 4"	94506004	C\$ 226.37
Clapper Assy, 6" DDX	71041601	C\$ 9,225.32
Cover, 6"	92116066	C\$ 1,278.93
Seal Faceplate Subassembly, 6"	93416006	C\$ 916.80
Gasket, Cover, 6"	93706006	C\$ 270.03
O-ring - Need to order 014	95406407	C\$ 46.09
O-ring - Need to order 114	95406007	C\$ 46.09
O-ring - Need to order 912	95406024	C\$ 46.09
Hinge Pin, Clapper	96216086	C\$ 182.27
Piston	95106006	C\$ 1,326.07
Pushrod	95506006	C\$ 894.97
Pushrod Guide	93916006	C\$ 193.19
Ring, Retaining (2 Assembled to Item No.14)	95306267	C\$ 20.09
Screw, Hex Cap, Ø ½"-13 x 1-1/2"	95606107	C\$ 49.99
Screw, Hex Cap, Ø 5/8"-11 x 1-3/4"	91106006	C\$ 49.99
Spring Lock Washer, #10	96906111	C\$ 5.23
Screw, C'sunk Cap Head, Ø 3/8"-16 x ¾"	95606127	C\$ 49.99
Screw, Socket Head, #10-32 x 1"	95606130	C\$ 49.99
Screw, Socket Head, Ø ¼"-20 x 5/8"	95606114	C\$ 49.99
Spring, Lever	96406004	C\$ 98.46
Spring	96406906	C\$ 109.37
Diaphragm	95276006	C\$ 136.01
Knob, Reset, Assembly	94356007	C\$ 219.16

Description	Part Number	List Price
MODEL DDX — 8" DELUGE VALVE		
Pushrod Cover Assembly	71040416	C\$ 1,351.84
O-Ring - Need to order 256	95406414	C\$ 46.09
Screw, Hex Cap, 5/8-11x2"	95606110	C\$ 60.03
Mounting Ring, Machined	91306018	C\$ 87.54
Clapper, Machined	91916008	C\$ 6,695.85
Access Cover	92116068	C\$ 250.16
Seal Assembly	93416008	C\$ 442.24
Gasket, Access Cover	93706008	C\$ 270.03
Bumpstop Assembly	93722000	C\$ 191.21
Pushrod Guide	93916006	C\$ 193.19
Lever	94506008	C\$ 1,617.27
Striker	95006410	C\$ 1,591.08
Piston	95106006	C\$ 1,326.07
Diaphragm	95276006	C\$ 136.01
Retaining Clip, 3/4" Shaft	95316408	C\$ 124.21
O-Ring - Need to order 114	95406007	C\$ 46.09
O-Ring - Need to order 912	95406024	C\$ 46.09
O-Ring - Need to order 260	95406407	C\$ 46.09
O-Ring - Need to order 259	95406413	C\$ 46.09
Screw, Socket Head, 1/4-20 x 5/8"	95606114	C\$ 49.99
Screw, Socket Head, #10-32 x 1"	95606130	C\$ 49.99
Seat, Machined	96016008	C\$ 1,547.84
Hinge Pin	96206008	C\$ 218.73
Lever Pin	96216008	C\$ 895.84
Clapper Spacer	96310008	C\$ 218.73
Lever Spring	96406008	C\$ 118.09
DDX Spring	96406906	C\$ 109.37
Spring Lock Washer, #10	96906111	C\$ 5.23
Screw, Socket Cap, Flat Head, 1/2-13 x 3/4"	95606135	C\$ 44.97
Reset Knob Assembly	94356007	C\$ 219.16

Description	Part Number	List Price
MODEL DDX — 8" STAINLESS STEEL DELUGE VALVE		
Pushrod Cover	92126358	C\$ 601.83
O-Ring - Need to order 266	95406414	C\$ 46.09
Screw, Hex Cap, 5/8-11x2"	95606137	C\$ 60.03
Mounting Ring, Machined	91326018	C\$ 87.54
Clapper, Machined	91926008	C\$ 7,236.54
Access Cover	92126069	C\$ 270.49
Seal Assembly	93416028	C\$ 473.23
Gasket, Access Cover	93706008	C\$ 270.03
Bumpstop Assembly	93722000	C\$ 191.21
DDX:PUSHROD GUIDE	93916006	C\$ 193.19
LEVER,8" DDX VALVE 6-4, GRADE 5	94506028	C\$ 1,887.28
Striker	95006411	C\$ 1,622.28
Piston	95106006	C\$ 1,326.07
Diaphragm	95276006	C\$ 136.01
Retaining Clip, 3/4" Shaft	95316408	C\$ 124.21
O-Ring - Need to order 114	95406007	C\$ 46.09
O-Ring - Need to order 912	95406024	C\$ 46.09
O-Ring - Need to order 260	95406407	C\$ 46.09
O-Ring - Need to order 259	95406413	C\$ 46.09
Screw, Socket Head, 1/4-20 x 5/8"	95606114	C\$ 49.99
Screw, Socket Head, #10-32 x 1"	95606130	C\$ 49.99
Seat, Machined	96026008	C\$ 1,600.68
Hinge Pin	96206008	C\$ 218.73
Lever Pin	96216008	C\$ 895.84
Clapper Spacer	96310008	C\$ 218.73
Lever Spring	96406008	C\$ 118.09
DDX Spring	96406906	C\$ 109.37
Spring Lock Washer, #10	96906111	C\$ 5.23
Screw, Socket Cap, Flat Head, 1/2-13 x 3/4"	95606135	C\$ 44.97
Reset Knob Assembly	94356009	C\$ 273.07

Description	Part Number	List Price
MODEL BX — 4" & 6" EXTERNAL RESET DEVICE		
Reset Knob Ext. Reset Del Mod. B 4" & 6"	94356426	C\$ 236.19
"O" Ring Shaft Ext. Reset 4" & 6" Del	95406425	C\$ 6.99
"O" Ring Bearing 4" & 6" Del Mod. B Ext. Res.		C\$ Call
Screw Spring 4" Del Ext. Reset	95606424	C\$ 12.20
Lever Screw Ext Reset Del Valve 4" & 6"	95606426	C\$ 79.46
Stud Threaded, BX 4" & 6" Del Ext. Reset		C\$ Call
Clapper Spring, 4" & 6" Del BX		C\$ Call
MODEL B — DELUGE VALVE TRIM PARTS		
Drip Cup, Support Clip Bolt, Nut & Screw	71010471	C\$ 494.64
Strainer 3/4"	78650200	C\$ 470.19
Stop Cock Valve 1/2"	78650300	C\$ 427.63
Ball Drip Valve 1/2" Mechanical Mod. C	78653100	C\$ 800.03
Strainer 1/4"		C\$ Call
Angle Valve 2"	98840100	C\$ 797.83
Horizontal Check Valve 1/4"	98840143	C\$ 461.03
Globe Valve 1/2"	98840171	C\$ 404.71
Horizontal Check Valve 1/2"	98840181	C\$ 442.70
Globe Valve 1/4"	98840172	C\$ 394.00
Pressure Switch	98728800	C\$ 1,853.03
Restrictor Check Valve	98840141	C\$ 595.91
Air Pressure Gauge	98248000	C\$ 201.90
Water Pressure Gauge	98248001	C\$ 188.83
1/4" 3 Way Bronze Gauge Valve - Need to order 2	98840160	C\$ 336.83
Relief Valve Bronze 1/2"		C\$ Call
Actuator Diaphragm	92206311	C\$ 169.39
Actuator Face Plate	95106901	C\$ 191.44
Actuator Face Plate Assembly	95106911	C\$ 169.39
1/4" 3 Way Bronze Gauge Valve	98840160	C\$ 336.83
MODEL A 2 — AUTOMATIC AIR MAINTENANCE DEVICE		
Regulator	98681630	C\$ 1,056.04
Strainer 1/4"	98727606	C\$ 326.11
Check Valve 1/4"	96816902	C\$ 472.61
Globe Valve 3/4"	98840170	C\$ 461.03
Globe Valve 1/4" - Need to order 2	98840172	C\$ 394.00
Restriction Nipple 1/4"	98523100	C\$ 101.50