

RASCOLOOP

Model RLP RASCOLOOP U-Type Seismic Expansion Joint with Grooved Outlets

Description	Part Number	Short Code	List Price
GROOVE END (+/- 4" MOVEMENT)			
RASCOLOOP,#RLP-1G4,1,GROOVED,+/-4	7M99004967	RLP1G4	C\$ 2,717.71
RASCOLOOP,#RLP-125G4,1.25,GROOVED,+/-4	7M99004970	RLP125G4	C\$ 3,066.02
RASCOLOOP,#RLP-15G4,1.5,GROOVED,+/-4	7M99004973	RLP15G4	C\$ 3,397.11
RASCOLOOP,#RLP-2G4,2,GROOVED,+/-4	7M99004976	RLP2G4	C\$ 4,456.57
RASCOLOOP,#RLP-25G4,2.5,GROOVED,+/-4	7M99004979	RLP25G4	C\$ 4,751.85
RASCOLOOP,#RLP-3G4,3,GROOVED,+/-4	7M99004982	RLP3G4	C\$ 5,688.63
RASCOLOOP,#RLP-4G4,4,GROOVED,+/-4	7M99004985	RLP4G4	C\$ 8,322.56
RASCOLOOP,#RLP-6G4,6,GROOVED,+/-4	7M99004988	RLP6G4	C\$ 15,974.96
RASCOLOOP,#RLP-8G4,8,GROOVED,+/-4	7M99004991	RLP8G4	C\$ 23,774.50
RASCOLOOP,#RLP-10G4,10,GROOVED,+/-4	7M99004994	RLP10G4	C\$ 35,493.80
GROOVE END (+/- 8" MOVEMENT)			
RASCOLOOP,#RLP-1G8,1,GROOVED,+/-8	7M99004968	RLP1G8	C\$ 2,838.53
RASCOLOOP,#RLP-125G8,1.25,GROOVED,+/-8	7M99004971	RLP125G8	C\$ 3,224.37
RASCOLOOP,#RLP-15G8,1.5,GROOVED,+/-8	7M99004974	RLP15G8	C\$ 3,918.16
RASCOLOOP,#RLP-2G8,2,GROOVED,+/-8	7M99004977	RLP2G8	C\$ 5,079.62
RASCOLOOP,#RLP-25G8,2.5,GROOVED,+/-8	7M99004980	RLP25G8	C\$ 5,577.66
RASCOLOOP,#RLP-3G8,3,GROOVED,+/-8	7M99004983	RLP3G8	C\$ 6,812.30
RASCOLOOP,#RLP-4G8,4,GROOVED,+/-8	7M99004986	RLP4G8	C\$ 9,691.57
RASCOLOOP,#RLP-6G8,6,GROOVED,+/-8	7M99004989	RLP6G8	C\$ 18,273.85
RASCOLOOP,#RLP-8G8,8,GROOVED,+/-8	7M99004992	RLP8G8	C\$ 26,979.43
RASCOLOOP,#RLP-10G8,10,GROOVED,+/-8	7M99004995	RLP10G8	C\$ 39,127.14
GROOVE END (+/- 16" MOVEMENT)			
RASCOLOOP,#RLP-1G16,1,GROOVED,+/-16	7M99004969	RLP1G16	C\$ 3,324.04
RASCOLOOP,#RLP-125G16,1.25,GROOVED,+/-16	7M99004972	RLP125G16	C\$ 3,810.88
RASCOLOOP,#RLP-15G16,1.5,GROOVED,+/-16	7M99004975	RLP15G16	C\$ 4,131.14
RASCOLOOP,#RLP-2G16,2,GROOVED,+/-16	7M99004978	RLP2G16	C\$ 5,564.49
RASCOLOOP,#RLP-25G16,2.5,GROOVED,+/-16	7M99004981	RLP25G16	C\$ 7,092.71
RASCOLOOP,#RLP-3G16,3,GROOVED,+/-16	7M99004984	RLP3G16	C\$ 8,506.00
RASCOLOOP,#RLP-4G16,4,GROOVED,+/-16	7M99004987	RLP4G16	C\$ 12,140.57
RASCOLOOP,#RLP-6G16,6,GROOVED,+/-16	7M99004990	RLP6G16	C\$ 23,218.99
RASCOLOOP,#RLP-8G16,8,GROOVED,+/-16	7M99004993	RLP8G16	C\$ 32,431.10
RASCOLOOP,#RLP-10G16,10,GROOVED,+/-16	7M99004996	RLP10G16	C\$ 45,085.95

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

Metraflex®



FIRELOOP

Expansion loop for fire sprinkler systems

Description	Part Number	List Price
THREAD END		
		C\$ Call
METRAFLEX,#MLUTFM80075 3/4" FL 4" MVMT	6999994166	C\$ 2,194.65
METRAFLEX,#MLUTFM80100 1" FL 4" MVMT	6999994167	C\$ 2,300.19
METRAFLEX,#MLUTFM80125 1.25" FL 4" MVMT	6999994168	C\$ 2,704.83
		C\$ Call
METRAFLEX,#MLUTFM80400 4" FL 4" MVMT	6999994173	C\$ 9,829.70
GROOVE END (+/- 4" MOVEMENT)		
METRAFLEX,#MLUGFM80200 2" FL 4" AX	6999994144	C\$ 5,664.73
METRAFLEX,#MLUGFM80250 2-1/2" FL 4" AX	6999994145	C\$ 6,293.66
METRAFLEX,#MLUGFM80300 3" FL 4" AX	6999994146	C\$ 8,048.49
METRAFLEX,#MLUGFM80400 4" FL 4" AX	6999994147	C\$ 10,119.99
METRAFLEX,#MLUGFM80500 5" FL 4" AX	6999994148	C\$ 13,972.70
METRAFLEX,#MLUGFM80600 6" FL 4" AX	6999994149	C\$ 19,382.34
METRAFLEX,#MLUGFM80800 8" FL 4" AX	6990020138	C\$ 30,654.62
GROOVE END (+/- 8" MOVEMENT)		
METRAFLEX,#MLUGFM160200 2" FL 8" AX	6990001613	C\$ 6,078.15
METRAFLEX,#MLUGFM160250 2-1/2" FL 8" AX	6990001614	C\$ 6,751.06
METRAFLEX,#MLUGFM160300 3" FL 8" AX	6990001615	C\$ 9,131.25
METRAFLEX,#MLUGFM160400 4" FL 8" AX	6990001616	C\$ 10,836.87
METRAFLEX,#MLUGFM160500 5" FL 8" AX	6990001617	C\$ 14,949.08
METRAFLEX,#MLUGFM160600 6" FL 8" AX	6990001618	C\$ 20,569.84
METRAFLEX,#MLUGFM160800 8" FL 8" AX	6990001619	C\$ 37,238.56

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.