

GATE VALVES

- See Bulletin 443



OSY L399GG



OSY L399FG

Description	Part Number	Short Code	List Price
RELIABLE OSY - L399GG GROOVED x GROOVED GATE VALVES			
RASCO,#REL-OSY-L399GG,2",300PSI,GXG	7M99004056	2ROSYGG	\$ 2,603.30
RASCO,#REL-OSY-L399GG,2.5",300PSI,GXG	7M99004057	25ROSYGG	\$ 2,704.23
RASCO,#REL-OSY-L399GG,3",300PSI,GXG	7M99004058	3ROSYGG	\$ 2,869.75
RASCO,#REL-OSY-L399GG,4",300PSI,GXG	7M99004059	4ROSYGG	\$ 3,307.53
RASCO,#REL-OSY-L399GG,6",300PSI,GXG	7M99004061	6ROSYGG	\$ 5,038.96
RASCO,#REL-OSY-L399GG,8",300PSI,GXG	7M99004062	8ROSYGG	\$ 8,297.81
RASCO,#REL-OSY-L399GG,10",300PSI,GXG	7M99004063	10ROSYGG	\$12,471.36
RASCO,#REL-OSY-L399GG,12",300PSI,GXG	7M99004064	12ROSYGG	\$18,521.95
RELIABLE OSY - L399F FLANGE x FLANGE GATE VALVES			
RASCO,#REL-OSY-L399F,2",300PSI,FXF	7M99004038	2ROSY	\$ 2,603.30
RASCO,#REL-OSY-L399F,2.5",300PSI,FXF	7M99004039	25ROSY	\$ 2,704.23
RASCO,#REL-OSY-L399F,3",300PSI,FXF	7M99004040	3ROSY	\$ 2,869.75
RASCO,#REL-OSY-L399F,4",300PSI,FXF	7M99004041	4ROSY	\$ 3,307.53
RASCO,#REL-OSY-L399F,6",300PSI,FXF	7M99004043	6ROSY	\$ 5,038.96
RASCO,#REL-OSY-L399F,8",300PSI,FXF	7M99004044	8ROSY	\$ 8,297.81
RASCO,#REL-OSY-L399F,10",300PSI,FXF	7M99004045	10ROSY	\$12,471.36
RASCO,#REL-OSY-L399F,12",300PSI,FXF	7M99004046	12ROSY	\$18,521.95
RELIABLE OSY - L399FG FLANGE x GROOVED GATE VALVES			
RASCO,#REL-OSY-L399FG,2",300PSI,FXG	7M99004047	2ROSYFG	\$ 2,603.30
RASCO,#REL-OSY-L399FG,2.5",300PSI,FXG	7M99004048	25ROSYFG	\$ 2,704.23
RASCO,#REL-OSY-L399FG,3",300PSI,FXG	7M99004049	3ROSYFG	\$ 2,869.75
RASCO,#REL-OSY-L399FG,4",300PSI,FXG	7M99004050	4ROSYFG	\$ 3,307.53
RASCO,#REL-OSY-L399FG,6",300PSI,FXG	7M99004052	6ROSYFG	\$ 5,038.96
RASCO,#REL-OSY-L399FG,8",300PSI,FXG	7M99004053	8ROSYFG	\$ 8,297.81
RASCO,#REL-OSY-L399FG,10",300PSI,FXG	7M99004054	10ROSYFG	\$12,471.36
RASCO,#REL-OSY-L399FG,12",300PSI,FXG	7M99004055	12ROSYFG	\$18,521.95
RELIABLE PIUP - 388 INDICATOR POST UNDERGROUND TYPE			
RASCO,#REL-PIUP-388,VERTICAL IND POST	7M99003232	RVPI	\$ 6,323.19
RELIABLE W388 INDICATOR POST WALL TYPE			
RASCO,#REL-PIW-388,WALL-TYPE IND POST	7M99003233	RWPI	\$ 4,215.46
RASCO,STEM/COUP UNIT,WALL-TYPE IND POST	7M99003657	STEMRWPI	\$ 525.37
RELIABLE REPLACEMENT HANDWHEEL			
RASCO,REPL.HANDWHEEL,2"-2.5" OSY	7M99003825		\$ 207.61
RASCO,REPL.HANDWHEEL,5"-6" OSY	7M99003826		\$ 248.53
RASCO,REPL.HANDWHEEL,8" OSY	7M99003827		\$ 311.44
RASCO,REPL.HANDWHEEL,10",OSY	7M99003828		\$ 644.91
RASCO,REPL.HANDWHEEL,WALL POST IND	7M99003829		\$ 644.91
RELIABLE FCV - L501F SWING CHECK VALVE			
RASCO,#REL-FCV-L501F,2",300PSI,FXF,CHK	7M99004094	2CVF	\$ 2,103.88
RASCO,#REL-FCV-L501F,2.5",300PSI,FXF,CHK	7M99004095	25CVF	\$ 2,462.41
RASCO,#REL-FCV-L501F,3",300PSI,FXF,CHK	7M99004096	3CVF	\$ 3,079.10
RASCO,#REL-FCV-L501F,4",300PSI,FXF,CHK	7M99004097	4CVF	\$ 4,532.48
RASCO,#REL-FCV-L501F,6",300PSI,FXF,CHK	7M99004099	6CVF	\$ 8,098.87
RASCO,#REL-FCV-L501F,8",300PSI,FXF,CHK	7M99004100	8CVF	\$13,811.68
RASCO,#REL-FCV-L501F,10",300PSI,FXF,CHK	7M99004101	10CVF	\$19,927.47
RASCO,#REL-FCV-L501F,12",300PSI,FXF,CHK	7M99004102	12CVF	\$27,724.77

GATE VALVES / RELIABLE PIV



RBVT THREADED BUTTERFLY VALVE

- See Bulletin 830



RBVG GROOVED BRONZE VALVE

Description	Part Number	Short Code	List Price
RELIABLE PIV - L388F FLANGE x FLANGE GATE VALVES			
RASCO,#REL-PIV-L388F,2",300PSI,FXF	7M99004065	2RPIV	\$ 3,210.21
RASCO,#REL-PIV-L388F,2.5",300PSI,FXF	7M99004066	25RPIV	\$ 3,210.21
RASCO,#REL-PIV-L388F,3",300PSI,FXF	7M99004067	3RPIV	\$ 3,210.21
RASCO,#REL-PIV-L388F,4",300PSI,FXF	7M99004068	4RPIV	\$ 3,210.21
RASCO,#REL-PIV-L388F,6",300PSI,FXF	7M99004070	6RPIV	\$ 4,893.06
RASCO,#REL-PIV-L388F,8",300PSI,FXF	7M99004071	8RPIV	\$ 8,122.82
RASCO,#REL-PIV-L388F,10",300PSI,FXF	7M99004072	10RPIV	\$ 12,159.93
RASCO,#REL-PIV-L388F,12",300PSI,FXF	7M99004073	12RPIV	\$ 16,803.27
RELIABLE PIV - L388FG FLANGE x GROOVED GATE VALVES			
RASCO,#REL-PIV-L388FG,2",300PSI,FXG	7M99004074	2RPIVFG	\$ 3,210.21
RASCO,#REL-PIV-L388FG,2.5",300PSI,FXG	7M99004075	25RPIVFG	\$ 3,210.21
RASCO,#REL-PIV-L388FG,3",300PSI,FXG	7M99004076	3RPIVFG	\$ 3,210.21
RASCO,#REL-PIV-L388FG,4",300PSI,FXG	7M99004077	4RPIVFG	\$ 3,210.21
RASCO,#REL-PIV-L388FG,8",300PSI,FXG	7M99004080	8RPIVFG	\$ 8,122.82
RASCO,#REL-PIV-L388FG,10",300PSI,FXG	7M99004081	10RPIVFG	\$ 12,159.93
RASCO,#REL-PIV-L388FG,12",300PSI,FXG	7M99004082	12RPIVFG	\$ 16,803.27
RELIABLE PIV - L388GG GROOVED x GROOVED GATE VALVES			
RASCO,#REL-PIV-L388GG,2.5",300PSI,GXG	7M99004086	25RPIVGG	\$ 3,210.21
RASCO,#REL-PIV-L388GG,3",300PSI,GXG	7M99004087	3RPIVGG	\$ 3,210.21
RASCO,#REL-PIV-L388GG,4",300PSI,GXG	7M99004088	4RPIVGG	\$ 3,210.21
RASCO,#REL-PIV-L388GG,6",300PSI,GXG	7M99004090	6RPIVGG	\$ 4,893.06
RASCO,#REL-PIV-L388GG,8",300PSI,GXG	7M99004091	8RPIVGG	\$ 8,122.82
RASCO,#REL-PIV-L388GG,10",300PSI,GXG	7M99004092	10RPIVGG	\$ 12,159.93
RASCO,#REL-PIV-L388GG,12",300PSI,GXG	7M99004093	12RPIVGG	\$ 16,803.27
RELIABLE RBVT THREADED BRONZE BUTTERFLY VALVE			
RASCO,#REL-BBVT1,1",THRD,300PSI	7M99004562	B1R	\$ 909.32
RASCO,#REL-BBVT125,1.25",THRD,300PSI	7M99004563	B125R	\$ 980.88
RASCO,#REL-BBVT15,1.5",THRD,300PSI	7M99004564	B15R	\$ 1,049.89
RASCO,#REL-BBVT2,2",THRD,300PSI	7M99004565	B2R	\$ 1,236.93
RASCO,#REL-BBVT25,2.5",THRD,300PSI	7M99004566	B25R	\$ 1,577.16
RELIABLE RBVG GROOVED BRONZE VALVE			
RASCO,#REL-BBVG125,1.25",GRV,300PSI	7M99004567	BG125R	\$ 1,025.47
RASCO,#REL-BBVG15,1.5",GRV,300PSI	7M99004568	BG15R	\$ 1,086.14
RASCO,#REL-BBVG2,2",GRV,300PSI	7M99004569	BG2R	\$ 1,228.54
RASCO,#REL-BBVG25,2.5",GRV,300PSI	7M99004570	BG25R	\$ 1,421.34
RELIABLE REPLACEMENT HANDWHEEL			
RASCO,REPL.HANDWHEEL,2"-2.5" OSY	7M99003825		\$ 207.61
RASCO,REPL.HANDWHEEL,5"-6" OSY	7M99003826		\$ 248.53
RASCO,REPL.HANDWHEEL,8" OSY	7M99003827		\$ 311.44
RASCO,REPL.HANDWHEEL,10",OSY	7M99003828		\$ 644.91
RASCO,REPL.HANDWHEEL,WALL POST IND	7M99003829		\$ 644.91
RELIABLE FCV - L501F SWING CHECK VALVE			
RASCO,#REL-FCV-L501F,2",300PSI,FXF,CHK	7M99004094	2CVF	\$ 2,103.88
RASCO,#REL-FCV-L501F,2.5",300PSI,FXF,CHK	7M99004095	25CVF	\$ 2,462.41
RASCO,#REL-FCV-L501F,3",300PSI,FXF,CHK	7M99004096	3CVF	\$ 3,079.10
RASCO,#REL-FCV-L501F,4",300PSI,FXF,CHK	7M99004097	4CVF	\$ 4,532.48
RASCO,#REL-FCV-L501F,6",300PSI,FXF,CHK	7M99004099	6CVF	\$ 8,098.87
RASCO,#REL-FCV-L501F,8",300PSI,FXF,CHK	7M99004100	8CVF	\$ 13,811.68
RASCO,#REL-FCV-L501F,10",300PSI,FXF,CHK	7M99004101	10CVF	\$ 19,927.47
RASCO,#REL-FCV-L501F,12",300PSI,FXF,CHK	7M99004102	12CVF	\$ 27,724.77

RELIABLE BUTTERFLY VALVES



**REL300GT
BUTTERFLY VALVE
- NORMALLY OPEN**

- See Bulletin 833



**REL300GT
BUTTERFLY VALVE
- NORMALLY
CLOSED**

- See Bulletin 833



**REL363GT
BUTTERFLY VALVE
- NORMALLY OPEN**

- See Bulletin 835



**REL363GT
BUTTERFLY VALVE
- NORMALLY
CLOSED**

- See Bulletin 835

Description	Part Number	Short Code	List Price
RELIABLE BFG-300GT BUTTERFLY VALVES NORMALLY OPEN			
RASCO,#REL300GT,2 1/2",GRV BFV	7M99004895	25RBG300T	\$ 880.64
RASCO,#REL300GT,3",GRV BFV	7M99004896	3RBG300T	\$ 913.65
RASCO,#REL300GT,4",GRV BFV	7M99004897	4RBG300T	\$ 1,032.79
RASCO,#REL300GT,6",GRV BFV	7M99004898	6RBG300T	\$ 1,488.09
RASCO,#REL300GT,8",GRV BFV	7M99004899	8RBG300T	\$ 1,971.67
RELIABLE BFG-300GTC BUTTERFLY VALVES NORMALLY CLOSED			
RASCO,#REL300GTC,2 1/2",GRV BFV,NC	7M99004900	25RBG300NCT	\$ 906.88
RASCO,#REL300GTC,3",GRV BFV,NC	7M99004901	3RBG300NCT	\$ 931.65
RASCO,#REL300GTC,4",GRV BFV,NC	7M99004902	4RBG300NCT	\$ 1,057.90
RASCO,#REL300GTC,6",GRV BFV,NC	7M99004903	6RBG300NCT	\$ 1,506.62
RASCO,#REL300GTC,8",GRV BFV,NC	7M99004904	8RBG300NCT	\$ 1,992.25

Description	Part Number	Short Code	List Price
RELIABLE BFG-363GT BUTTERFLY VALVES NORMALLY OPEN			
RASCO,#REL363GT,2",GRV BFV	7M99004960	2RBG363T	\$ 1,092.44
RASCO,#REL363GT,2 1/2",GRV BFV	7M99004905	25RBG363T	\$ 1,092.44
RASCO,#REL363GT,3",GRV BFV	7M99004906	3RBG363T	\$ 1,133.40
RASCO,#REL363GT,4",GRV BFV	7M99004907	4RBG363T	\$ 1,269.95
RASCO,#REL363GT,6",GRV BFV	7M99004908	6RBG363T	\$ 1,829.83
RASCO,#REL363GT,8",GRV BFV	7M99004909	8RBG363T	\$ 2,403.36
RASCO,#REL363GT,10",GRV BFV	7M99004959	10RBG363T	\$ 4,503.65
RELIABLE BFG-363GTC BUTTERFLY VALVES NORMALLY CLOSED			
RASCO,#REL363GTC,2",GRV BFV,NC	7M99004961	2RBG363NCT	\$ 1,125.01
RASCO,#REL363GTC,2 1/2",GRV BFV,NC	7M99004910	25RBG363NCT	\$ 1,125.01
RASCO,#REL363GTC,3",GRV BFV,NC	7M99004911	3RBG363NCT	\$ 1,155.75
RASCO,#REL363GTC,4",GRV BFV,NC	7M99004912	4RBG363NCT	\$ 1,289.49
RASCO,#REL363GTC,6",GRV BFV,NC	7M99004913	6RBG363NCT	\$ 1,836.50
RASCO,#REL363GTC,8",GRV BFV,NC	7M99004914	8RBG363NCT	\$ 2,428.45
RASCO,#REL363GTC,10",GRV BFV,NC	7M99004966	10RBG363NCT	\$ 4,503.65

Notes:

Specify the following when ordering:

Supervision

- Valve Supervised Open

- Valve Supervised Closed

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.