

## ELECTRICAL COMPONENTS



Description	Part Number	Short Code	List Price
<b>MODEL WFDT - WATERFLOW DETECTOR</b>			
SAFE SIG,WFDTN,1"-2",W/1" NPT	7M99003216	TTAPN	A\$ 563.38
<b>MODEL WFD CPVC FLOW SWITCH</b>			
SAFE SIG,WFDNFS,GLUE-IN CPVC	7M99003838	WFDNFS	A\$ 633.80
SAFE SIG,WFDNFT,THREADED-CPVC	7M99003839	WFDNFT	A\$ 633.80
<b>MODEL WFDN - WATERFLOW DETECTOR</b>			
SAFE SIG,WFD20N,2"	7M99003209	2WDN	A\$ 556.34
SAFE SIG,WFD25N,2.5"	7M99003210	25WDN	A\$ 556.34
SAFE SIG,WFD30N,3"	7M99003211	3WDN	A\$ 556.34
SAFE SIG,WFD40N,4"	7M99003212	4WDN	A\$ 556.34
SAFE SIG,WFD50N,5"	7M99003213	5WDN	A\$ 563.38
SAFE SIG,WFD60N,6"	7M99003214	6WDN	A\$ 556.34
SAFE SIG,WFD80N,8"	7M99003215	8WDN	A\$ 646.48
<b>MODEL EPS PRESSURE SWITCH</b>			
SS,PRS ALRM SWITCH #EPS10-1	6999991339	EPS10-1	A\$ 477.46
SS,PRS ALRM SWITCH #EPS10-2	6999991212	EPS10-2	A\$ 542.25
SS,EPRS ALRM SWITCH #EPS40-1	6999991213	EPS40-1	A\$ 477.46
SS,H/L PRS SUPV SW #EPS40-2	6999991340	EPS40-2	A\$ 542.25
<b>MODEL OSY2 - TAMPER SWITCH</b>			
SAFE SIG,TAMPER SWITCH,OSY2	6985010000	OST	A\$ 357.75
<b>MODEL PIB V2 - TAMPER SWITCH</b>			
SAFE SIG,TAMPER SWITCH PIBV2,NTFR	6985020000	PIT	A\$ 338.03
<b>MODEL PSP1 - TAMPER SWITCH</b>			
SAFE SIG,PSP1,SUPERVISORY SWITCH	6985030000	PSP1	A\$ 735.21
<b>WATERFLOW ACCESSORIES</b>			
SS,GSKT,1 & 1 1/2 WFD	6999990717		A\$ 35.21
SS,GSKT 2,3,3 1/2WFD,NOTIFIER 111-010	6999990357		A\$ 35.21
SS,GSKT 4,5,6,8,WFD,G07 111-0300	6999990356		A\$ 35.21
SAFE SIG,TIMER A3008-00 REPLACEMNT TIMER	6999992444	TIMER	A\$ 211.27
SAFE SIG,FS-RT,REPL. TERMINAL BLOCK	7M99003218	FSRT	A\$ 215.49
SAFE SIG,546-7000,TAMPER,WFD,OST,COVER	6923000000	5467000	A\$ 112.68
SAFE SIG,WFDW,WRENCH,COVER	6999990769	WFDW	A\$ 38.03
SS,#C58-164-01,REPL.COVER,WFD	6999991174		A\$ 54.65
<b>ELECTRIC ALARM BELLS-BRECCO</b>			
BRECCO,6",24V,ELECTRIC BELL	6990023215	6KMSB	A\$ 147.96
BRECCO,8",24V,ELECTRIC BELL	6990023216	8KMSB	A\$ 192.01
BRECCO,10",24V,ELECTRIC BELL	6990023217	10KMSB	A\$ 192.15
BRECCO,6",120V,ELECTRIC BELL	6990018984	6KBSB	A\$ 147.96
BRECCO,8",120V,ELECTRIC BELL	6990023218	8KBSB	A\$ 192.01
BRECCO,10",120V,ELECTRIC BELL	6990019017	10KBSB	A\$ 192.15
<b>ACCESSORIES AND SOUNDER STROBE</b>			
SYSEN,#P2RL,HORN/STROBE,RED,12-24V	6990006617	P2RL	A\$ 224.11
SYSEN,HORN/STROBE,#P2RHK-120,W/BACK BOX	6990001425	HORNWBB	A\$ 329.58
BRECCO,#ELBBB,WEATHER PROOF BACK BOX	6990018985	WBBB	A\$ 42.06

## ELECTRICAL COMPONENTS CANADIAN VERSIONS



Description	Part Number	List Price
<b>MODEL WFDTA - WATERFLOW DETECTOR</b>		
<b>SEE SC-105 FOR UL/ULC/FM APPROVED SWITCH</b>		
1" - 2" T-Tap Waterflow		
1" - 2" Threaded T-Tap Waterflow		
<b>MODEL WFDA - WATERFLOW DETECTOR</b>		
<b>SEE PAGE SC-105 ALL WFDN SWITCHES ARE UL/ULC/FM APPROVED</b>		
2"		
2-1/2"		
3"		
4"		
5"		
6"		
8"		
<b>MODEL EPSA PRESSURE SWITCH</b>		
EPSA10-1 x	6999992366	A\$ 490.85
EPSA10-2 x	6999992360	A\$ 563.38
EPSA40-1 x	6999992367	A\$ 490.85
EPSA40-2 x	6999992361	A\$ 563.38
EPSA120-1 x	6999992534	A\$ 600.70
EPSA120-2 x		A\$ Call
<b>MODEL OSY2A - TAMPER SWITCH</b>		
Supervisory Switch for OS & Y	6999992362	A\$ 401.41
<b>MODEL PIB V2A - TAMPER SWITCH</b>		
Supervisory Switch for PIV/Butterfly Valves		A\$ Call
<b>MODEL PSP1A - TAMPER SWITCH</b>		
Plug in style Supervisory Switch	6990007844	A\$ 757.75

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

## SYSTEM SENSOR ELECTRICAL/RELIABLE (EUROPE)

Description	Part Number	Short Code	List Price
<b>MODEL WFDTN - WATERFLOW DETECTOR</b>			
25 - 50mm / 1 - 2" #WFDTN T-TAP	6990017635	TTAPNOS	A\$ 461.18
<b>CPVC FLOWSWITCH</b>			
WFDNFS - GLUE IN STYLE	7M99003838	WFDNFS	A\$ 633.80
WFDNFT - THREAD IN STYLE	7M99003839	WFDNFT	A\$ 633.80
<b>MODEL WFDEN - WATERFLOW DETECTOR</b>			
50mm / 2"	6983020009	2WNVDS	A\$ 510.14
65mm / 2-1/2"	6983025009	25WNVDS	A\$ 510.14
80mm / 3"	6983030009	3WNVDS	A\$ 510.14
100mm / 4"	6983040009	4WNVDS	A\$ 510.14
125mm / 5"	6990017532	5WNOS	A\$ 538.18
150mm / 6"	6983060009	6WNVDS	A\$ 510.14
200mm / 8"	6983080009	8WNVDS	A\$ 605.27
<b>MODEL WFD - WATERFLOW DETECTOR - EXPLOSION PROOF</b>			
50mm / 2"			A\$ Call
65mm / 2-1/2"	6983025004		A\$ 6,901.41
80mm / 3"			A\$ Call
100mm / 4"			A\$ Call
150mm / 6"			A\$ Call
200mm / 8"	6983080004		A\$ 7,211.27
<b>PRESSURE SWITCHES</b>			
EPS10 -1	7U99001622		A\$ 360.80
SS,PRS ALRM SWITCH #EPS10-2	6999991212	EPS10-2	A\$ 542.25
SS,EPRS ALRM SWITCH #EPS40-1	6999991213	EPS40-1	A\$ 477.46
SS,H/L PRS SUPV SW #EPS40-2	6999991340	EPS40-2	A\$ 542.25
EPS10EXP - Explosion Proof	7U99001877	EPS10EXPOS	A\$ 3,430.92
EPS40EXP - Explosion Proof	7U99001916	EPS40EXPOS	A\$ 3,430.92
<b>MODEL OSY2</b>			
Supervisory Switch for OS&Y	7U99001402		A\$ 302.65
<b>MODEL PIB V2</b>			
Supervisory Switch for P.I.V./Butterfly Valves	7U99001625	PITOS	A\$ 286.23
<b>MODEL PSP1 - plug in type</b>			
Plug in style Supervisory Switch	7U99001633		A\$ 752.48
<b>ELECTRIC ALARM BELLS &amp; HORN/STROBE</b>			
<b>MODEL</b>			
SSM24-6	7U99001626	6KMSOS	A\$ 152.89
SSM24-8	7U99001627	8KMSOS	A\$ 191.20
SSM24-10	7U99001628	10KMSOS	A\$ 211.86
SSM120-6	7U99001629	6KBSOS	A\$ 152.89
SSM120-8	7U99001630	8KBSOS	A\$ 191.20
SSM120-10	7U99001631	10KBSOS	A\$ 211.86
WBB Weatherproof Back Box	7U99001632	WBBOS	A\$ 83.01

## SYSTEM SENSOR ELECTRICAL (UL, FM) (FAR EAST / AUSTRALIA)

Description	Part Number	Short Code	List Price
<b>MODEL WFDT - WATERFLOW DETECTOR</b>			
25 - 40mm / 1 - 1-1/2" Threaded T-Tap Waterflow	7A99000043		A\$ 290.14
<b>CPVC FLOWSWITCH</b>			
WFDNFS - GLUE IN STYLE	7M99003838	WFDNFS	A\$ 633.80
WFDNFT - THREAD IN STYLE	7M99003839	WFDNFT	A\$ 633.80
<b>MODEL WFD - WATERFLOW DETECTOR</b>			
50mm / 2"	7A99000044		A\$ 290.14
65mm / 2-1/2"	7A99000045		A\$ 290.14
80mm / 3"	7A99000046		A\$ 290.14
90mm / 3-1/2"			A\$ Call
100mm / 4"	7A99000048		A\$ 290.14
125mm / 5"	7A99000049		A\$ 263.38
150mm / 6"	7A99000050		A\$ 290.14
200mm / 8"	7A99000051		A\$ 308.45
<b>MODEL WFD - WATERFLOW DETECTOR - EXPLOSION PROOF</b>			
50mm / 2"			A\$ Call
65mm / 2-1/2"	6983025004		A\$ 6,901.41
80mm / 3"			A\$ Call
100mm / 4"			A\$ Call
150mm / 6"			A\$ Call
200mm / 8"	6983080004		A\$ 7,211.27
<b>PRESSURE SWITCHES</b>			
SS,PRS ALRM SWITCH #EPS10-1	6999991339	EPS10-1	A\$ 477.46
SS,PRS ALRM SWITCH #EPS10-2	6999991212	EPS10-2	A\$ 542.25
SS,EPRS ALRM SWITCH #EPS40-1	6999991213	EPS40-1	A\$ 477.46
SS,H/L PRS SUPV SW #EPS40-2	6999991340	EPS40-2	A\$ 542.25
EPS10EXP - Explosion Proof	7U99001877	EPS10EXPOS	A\$ 3,430.92
EPS40EXP - Explosion Proof	7U99001916	EPS40EXPOS	A\$ 3,430.92
<b>MODEL OSY2 - TAMPER SWITCH</b>			
Supervisory Switch for OS&Y	6985010000	OST	A\$ 357.75
<b>MODEL PIB V2 - TAMPER SWITCH</b>			
Supervisory Switch for PIV/Butterfly Valves	6985020000	PIT	A\$ 338.03
<b>MODEL PSP1 - TAMPER SWITCH</b>			
Plug in style Supervisory Switch	6985030000	PSP1	A\$ 735.21
<b>ELECTRIC ALARM BELLS &amp; HORN/STROBE</b>			
<b>MODEL</b>			
SSM24-6	7A99000055		A\$ 67.75
SSM24-8	7A99000056		A\$ 90.56
SSM24-10	7A99000057		A\$ 83.41
SSM12-6	7A99000058		A\$ 67.75
SSM12-8	7A99000059		A\$ 76.48
SSM12-10	7A99000060		A\$ 83.41
SSM120-6	7A99000061		A\$ 67.15
SSM120-8	7A99000062		A\$ 75.28
SSM120-10	7A99000063		A\$ 82.21

Description	Part Number	Short Code	List Price
<b>MODEL WFD - WATERFLOW DETECTOR</b>			
50mm / 2"	6990017528	2WNOS	A\$ 425.69
65mm / 2-1/2"	6990017529	25WNOS	A\$ 425.69
80mm / 3"	6990017530	3WNOS	A\$ 425.69
100mm / 4"	6990017531	4WNOS	A\$ 425.69
125mm / 5"	6990017532	5WNOS	A\$ 538.18
150mm / 6"	6990017533	6WNOS	A\$ 425.69
200mm / 8"	6990017534	8WNOS	A\$ 505.06
<b>CPVC FLOWSWITCH</b>			
WFDNFS - GLUE IN STYLE	7M99003838	WFDNFS	A\$ 633.80
WFDNFT - THREAD IN STYLE	7M99003839	WFDNFT	A\$ 633.80
<b>MODEL WFD - WATERFLOW DETECTOR - EXPLOSION PROOF</b>			
50mm / 2"			A\$ Call
65mm / 2-1/2"	6983025004		A\$ 6,901.41
80mm / 3"			A\$ Call
100mm / 4"			A\$ Call
150mm / 6"			A\$ Call
200mm / 8"	6983080004		A\$ 7,211.27
<b>PRESSURE SWITCHES</b>			
SS,PRS ALRM SWITCH #EPS10-1	6999991339	EPS10-1	A\$ 477.46
SS,PRS ALRM SWITCH #EPS10-2	6999991212	EPS10-2	A\$ 542.25
SS,EPRS ALRM SWITCH #EPS40-1	6999991213	EPS40-1	A\$ 477.46
SS,H/L PRS SUPV SW #EPS40-2	6999991340	EPS40-2	A\$ 542.25
EPS10EXP - Explosion Proof	7U99001877	EPS10EXPOS	A\$ 3,430.92
EPS40EXP - Explosion Proof	7U99001916	EPS40EXPOS	A\$ 3,430.92
<b>MODEL OSY2 - TAMPER SWITCH</b>			
Supervisory Switch for OS&Y	6985010000	OST	A\$ 357.75
<b>MODEL PIB V2 - TAMPER SWITCH</b>			
Supervisory Switch for PIV/Butterfly Valves	6985020000	PIT	A\$ 338.03
<b>MODEL PSP1 - TAMPER SWITCH</b>			
Plug in style Supervisory Switch	6985030000	PSP1	A\$ 735.21
<b>ELECTRIC ALARM BELLS &amp; HORN/STROBE</b>			
<b>MODEL</b>			
SSM24-6	7U99001626	6KMSOS	A\$ 152.89
SSM24-8	7U99001627	8KMSOS	A\$ 191.20
SSM24-10	7U99001628	10KMSOS	A\$ 211.86
SSM120-6	7U99001629	6KBSOS	A\$ 152.89
SSM120-8	7U99001630	8KBSOS	A\$ 191.20
SSM120-10	7U99001631	10KBSOS	A\$ 211.86
WBB Weatherproof Back Box	7U99001632	WBBOS	A\$ 83.01