

MERIT TEE-LETS



Description	Part Number	Short Code	Box Qty	List Price
M300 - TEE-LETS				
.5 x 1.25-2	7M99003845	51252O	350	A\$ 21.17
.5 x 2-2.5"	7703020810	5225O	350	A\$ 21.17
.5 x 2.5-8"	7703021032	5258O	350	A\$ 21.17
.75 x 1.25-2"	7M99003455	751252O	250	A\$ 21.17
.75 x 2-2.5"	7707030810	75225O	250	A\$ 21.17
.75 x 2.5-8"	7707031032	75258O	250	A\$ 21.17
1 x 1.25-1.5"	7709040506	112515O	175	A\$ 30.73
1 x 1.5-2"	7709040608	1152O	175	A\$ 30.73
1 X 2-2.5"	7709040810	1225O	175	A\$ 30.73
1 x 2.5-4"	7M99003457	1254O	175	A\$ 30.73
1 x 5-8"	7709042032	158O	175	A\$ 30.73
1.25 x 1.5-2"	7711050608	125152O	95	A\$ 51.62
1.25 x 2-2.5"	7711050810	125225O	95	A\$ 51.62
1.25 x 2.5-3"	7711051012	125253O	95	A\$ 51.62
1.25 x 3-4"	7711051216	12534O	95	A\$ 51.62
1.25 x 5-8"	7711052032	12558O	95	A\$ 51.62
1.5 x 1.5"	7713060600	1515O	65	A\$ 62.17
1.5 x 2"	7713060800	152O	65	A\$ 62.17
1.5 x 2.5"	7713061000	1525O	65	A\$ 62.17
1.5 x 3-4"	7713061216	1534O	65	A\$ 62.17
1.5 x 4"	7713061600	154O	65	A\$ 62.17
1.5 x 5-8"	7713062032	1558O	65	A\$ 62.17
2 x 2"	7715080800	22O	35	A\$ 82.01
2 x 2.5"	7715081000	225O	35	A\$ 82.01
2 x 3"	7715081200	23O	35	A\$ 82.01
2 x 4"	7715081600	24O	35	A\$ 82.01
2 x 5"	7715082000	25O	35	A\$ 82.01
2 x 6"	7715082400	26O	35	A\$ 82.01
2 x 8"	7715083200	28O	35	A\$ 82.01

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

MERIT TEE-LETS



Description	Part Number	Short Code	Box Qty	List Price
TEE-LETS (CONT.)				
2.5 x 2.5"	7717101000	2525O	20	A\$ 149.27
2.5 x 3"	7717101200	253O	20	A\$ 149.27
2.5 x 4"	7717101600	254O	20	A\$ 149.27
2.5 x 5"	7717102000	255O	20	A\$ 149.27
2.5 x 6"	7717102400	256O	20	A\$ 149.27
2.5 x 8"	7717103200	258O	20	A\$ 149.27
3 x 3"	7719121200	33O	10	A\$ 287.07
3 x 4"	7719121600	34O	10	A\$ 287.07
3 x 6"	7719122400	36O	10	A\$ 287.07
3 x 8"	7719123200	38O	10	A\$ 287.07
4 x 4"	7721161600	44O	10	A\$ 460.75
4 x 6"	7721162400	46O	10	A\$ 460.75
4 x 8"	7721163200	48O	10	A\$ 460.75

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

MERIT TEE-LETS



Description	Part Number	Short Code	Box Qty	List Price
MERIT GROOVED SHAPED NIPPLES - SCHEDULE 40				
1.25 x 1.25"	7607050500	125125GSN	80	A\$ 66.14
1.25 x 1.5"	7607050600	12515GSN	80	A\$ 66.14
1.25 x 2-2.5"	7607050810	125225GSN	80	A\$ 66.14
1.25 x 3-4"	7607051216	12534GSN	80	A\$ 66.14
1.25 x 5-8"	7607052032	12558GSN	80	A\$ 66.14
1.5 x 1.5"	7609060600	1515GSN	50	A\$ 71.46
1.5 x 2"	7609060800	152GSN	50	A\$ 71.46
1.5 x 2.5"	7609061000	1525GSN	50	A\$ 71.46
1.5 x 3-4"	7609061216	1534GSN	50	A\$ 71.46
1.5 x 5-8"	7609062032	1558GSN	50	A\$ 71.46
2 x 2"	7611080800	22GSN	30	A\$ 77.48
2 x 2.5"	7611081000	225GSN	30	A\$ 77.48
2 x 3"	7611081200	23GSN	30	A\$ 77.48
2 x 4"	7611081416	24GSN	30	A\$ 77.48
2 x 5"	7611082000	25GSN	30	A\$ 77.48
2 x 6"	7611082400	26GSN	30	A\$ 77.48
2 x 8"	7611083200	28GSN	30	A\$ 77.48
2.5 x 2.5"	7627101000	2525SN4	20	A\$ 109.65
2.5 x 3"	7627101200	253SN4	20	A\$ 109.65
2.5 x 3.5-4"	7627101416	25354SN4	20	A\$ 109.65
2.5 x 5"			20	A\$ Call
2.5 x 6"	7627102400	256SN4	20	A\$ 109.65
2.5 x 8"	7627103200	258SN4	20	A\$ 109.65
3 x 3"	7629121200	33SN4	15	A\$ 143.48
3 x 3.5"			15	A\$ Call
3 x 4"	7629121600	34SN4	15	A\$ 143.48
3 x 5"	7629122000	35SN4	15	A\$ 143.48
3 x 6"	7629122400	36SN4	15	A\$ 143.48
3 x 8"	7629123200	38SN4	15	A\$ 143.48
4 x 4"	7631161600	44SN4	5	A\$ 223.94
4 x 5"	7631162000	45SN4	5	A\$ 223.94
4 x 6"	7631162400	46SN4	5	A\$ 223.94
4 x 8"	7631163200	48SN4	5	A\$ 223.94
6 x 6"	7635242400	66SN4	2	A\$ 454.01
6 x 8"	7635243200	68SN4	2	A\$ 454.01
8 x 8"	7637323200	88SN4	1	A\$ 574.20

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

MERIT TEE-LETS



Description	Part Number	Short Code	Box Qty	List Price
MERIT GROOVED SHAPED NIPPLES - SCHEDULE 10				
2.5 x 2.5"	7613101000	2525GSN	20	A\$ 94.20
2.5 x 3"	7613101200	253GSN	20	A\$ 94.20
2.5 x 4"	7613101416	254GSN	20	A\$ 94.20
2.5 x 5"	7613102000	255GSN	20	A\$ 94.20
2.5 x 6"	7613102400	256GSN	20	A\$ 94.20
2.5 x 8"	7613103200	258GSN	20	A\$ 94.20
3 x 3"	7615121200	33GSN	15	A\$ 128.00
3 x 3.5"	7615121416	335GSN	15	A\$ 128.00
3 x 4"	7615121600	34GSN	15	A\$ 128.00
3 x 5"	7615122000	35GSN	15	A\$ 128.00
3 x 6"	7615122400	36GSN	15	A\$ 128.00
3 x 8"	7615123200	38GSN	15	A\$ 128.00
4 x 4"	7619161600	44GSN	5	A\$ 181.49
4 x 5"	7619162000	45GSN	5	A\$ 181.49
4 x 6"	7619162400	46GSN	5	A\$ 181.49
4 x 8"	7619163200	48GSN	5	A\$ 181.49
6 x 6"	7623242400	66GSN	2	A\$ 399.17
6 x 8"	7623243200	68GSN	2	A\$ 399.17

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

IMPORT OLETS



Description	Part Number	Short Code	Box Qty	List Price
MTM-40 ANVIL IMPORT OLETS				
STAR,MTM-40,.5 X 1.25-2,O-LET	7M99003847	51252OS	400	A\$ 19.87
STAR,MTM-40,.5 X 2-2.5,O-LET	7S03020810	5225OS	400	A\$ 19.87
STAR,MTM-40,.5 X 2.5-8,O-LET	7S03021032	5258OS	240	A\$ 19.87
STAR,MTM-40,.75 X 1.25"-2",O-LET	7M99003543	751252OS	240	A\$ 19.87
STAR,MTM-40,3/4X2-2.5,O-LET	7S07030810	75225OS	160	A\$ 19.87
STAR,MTM-40,.75 X 2.5-8,O-LET	7S07031032	75258OS	160	A\$ 19.87
STAR,MTM-40,1 X 1.25 - 1.5,O-LET	7S09040506	112515OS	160	A\$ 29.00
STAR,MTM-40,1 X 1.5 - 2,O-LET	7S09040608	1152OS	160	A\$ 29.00
STAR,MTM-40,1X2-2.5,O-LET	7S09040810	1225OS	90	A\$ 29.00
STAR,MTM-40,1" X 2.5"-4",O-LET	7M99003545	1254OS	90	A\$ 29.00
STAR,MTM-40,1 X 5-8,O-LET	7S09042032	158OS	90	A\$ 29.00
STAR,MTM-40,1.25 X 1.25,O-LET	7S11050500	125125OS	90	A\$ 49.14
STAR,MTM-40,1.25X1.5-2,O-LET	7S11050608	125152OS	70	A\$ 49.14
STAR,MTM-40,1.25 X 2-2.5,O-LET	7S11050810	125225OS	70	A\$ 49.14
STAR,MTM-40,1.25X2.5-3,O-LET	7S11051012	125253OS	70	A\$ 49.14
STAR,MTM-40,1.25X3-4,O-LET	7S11051016	12534OS	70	A\$ 49.14
STAR,MTM-40,1.25 X 5-8,O-LET	7S11052032	12558OS	70	A\$ 49.14
STAR,MTM-40,1.5 X 1.5,O-LET	7S13060600	1515OS	70	A\$ 59.46
STAR,MTM-40,1.5 X 2,O-LET	7S13060800	152OS	40	A\$ 59.46
STAR,MTM-40,1.5 X 2.5,O-LET	7S13061000	1525OS	40	A\$ 59.46
STAR,MTM-40,1.5X3-4,O-LET	7S13061216	1534OS	40	A\$ 59.46
STAR,MTM-40,1.5 X 4,O-LET	7S13061600	154OS	40	A\$ 59.46
STAR,MTM-40,1.5X5-8,O-LET	7S13062032	1558OS	40	A\$ 59.46
STAR,MTM-40,2 X 2,O-LET	7S15080800	22OS	40	A\$ 78.58
STAR,MTM-40,2 X 2.5,O-LET	7S15081000	225OS	40	A\$ 78.58
STAR,MTM-40,2X3,O-LET	7S15081200	23OS	40	A\$ 78.58
STAR,MTM-40,2X4,O-LET	7S15081600	24OS	40	A\$ 78.58
STAR,MTM-40,2 X 6,O-LET	7S15082400	26OS	40	A\$ 78.58
STAR,MTM-40,2 X 8,O-LET	7S15083200	28OS	40	A\$ 78.58

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

Σ SIGMA

Piping Products

Description	Part Number	Short Code	List Price
SLIP ON WELD FLANGE			
2" (6OD)	6999992899	2SWF	A\$ 96.13
2-1/2" (7OD)			A\$ Call
3" (7-1/2OD)			A\$ Call
4" (9OD)			A\$ Call
6" (11OD)			A\$ Call
8" (13-1/2OD)			A\$ Call
10" (16OD)	6999992905	10SWF	A\$ 898.62
12" (19OD)			A\$ Call

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.