



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar)
Rated Pressure
- Adjusted with Pilot
Operated Regulator
- Trim Includes Relief
Valve
- No Trim
Connections to
Cover
- cULus listed and
FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	\$S\$13,996.76
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		\$S\$15,269.19
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		\$S\$15,269.19
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		\$S\$15,269.19
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		\$S\$15,269.19
1-1/2" ISO7-1 Thread/Thread	6507608000		\$S\$15,269.19
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	\$S\$13,996.76
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		\$S\$15,269.19
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		\$S\$15,269.19
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		\$S\$15,269.19
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		\$S\$15,269.19
2" ISO7-1 Thread/Thread	6507628000		\$S\$15,269.19
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	\$S\$16,223.51
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		\$S\$16,223.51
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		\$S\$17,655.00
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		\$S\$17,655.00
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		\$S\$17,655.00
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		\$S\$17,655.00
2-1/2" ISO7-1 Thread/Thread	6507618000		\$S\$17,655.00
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	\$S\$16,223.51
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		\$S\$17,655.00
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		\$S\$17,655.00
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		\$S\$17,655.00
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		\$S\$17,655.00
3" ISO7-1 Thread/Thread	6507638000		\$S\$17,655.00
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	\$S\$19,404.59
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		\$S\$21,154.19
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		\$S\$21,154.19
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		\$S\$21,154.19
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	\$S\$23,858.11
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		\$S\$23,858.11
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		\$S\$26,243.92
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		\$S\$26,243.92
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		\$S\$26,243.92

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

- "0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges
- "1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges
- "2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges
- "3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges