

# RFC49plus

Model RFC49plus & RFC49LLplus Residential  
Flat Plate Concealed Sprinklers

## Master the Unexpected

Introducing the RFC49plus: great Reliable® flows, now with one full inch vertical cover plate adjustment.

- Industry-leading 1" (25 mm) vertical cover plate adjustment
- Robust fusible link operating element with temperature ratings of 165°F (74°C) or 212°F (100°C)
- Wrenchable cap, saving installation time and providing protection of the sprinkler from the factory to finished ceiling installation
- Sturdy, smooth-edged G5 cover plate available in standard, special application, woodgrain, and custom printed or painted finishes



### Minimum Flow and Residual Pressure

| Max. Coverage Area ft x ft (m x m) | Flow gpm (l/min) | Pressure psi (bar) |
|------------------------------------|------------------|--------------------|
| 16x16 (4.9x4.9)                    | 13 (49.0)        | 7.0 (0.48)         |
| 18x18 (5.5x5.5)                    | 17 (64.3)        | 12.0 (0.83)        |
| 20x20 (6.1x6.1)                    | 20 (75.7)        | 16.7 (1.15)        |

**Reliable®**



See more at  
[reliablesprinkler.com/rfcplus](http://reliablesprinkler.com/rfcplus)

# COVER PLATE FINISHES



## Standard Finish



Chrome Plated



White Paint

## Standard Woodgrain Finish



White Wash



Silver Birch



Beige Birch

## Special Application Finish



Off White



Black Paint



Bright Brass



Finished Bronze



Satin Chrome



Stainless Steel Clad



Golden Pine



Red Oak



Warm Maple



Red Cherry



Dark Walnut



Espresso



Rustic Beige



Weathered Grey



Slate Grey

## Custom Paint & Prints



The only limit is your imagination!

See Bulletin 203 for details. Printed Finishes' hue shown may vary due to print and screen variation.

**Reliable**<sup>®</sup>

[reliablesprinkler.com/covers](http://reliablesprinkler.com/covers)