



Install 1 Sprinkler - Instead of 2 or More


The DH56 & DH80
Extended Coverage Horizontal Sidewalls




Light Hazard, Extended Coverage for Decks, Halls or Rooms




- * Less Sprinklers
- * Less Fittings
- * Less Holes to Cut
- * Less Labor
- * Less Potential for Problems



- * Calculate as few as 3 Sprinklers (75 linear feet) in Corridors
- * 250 psi rated
- * Polyester Coated Versions are cULus Corrosion Resistant



▲ Standard SW - 14'x14'
▲ DH80 for 28'x14' or DH56 for 28'x8' & 28'x10'



Sprinkler	Max. Spacing	Flow	Pressure
DH56 wet or dry	28' x 8'	23 gpm	16.9 psi
DH56 wet or dry	28' x 10'	28 gpm	25.0 psi
DH80 wet only	28' x 14'	40 gpm	25.0 psi

Please refer to Bulletins 003, 015, and 016

P/N 9999970406