



FP PUSH-ON/THREAD-OFF ESCUTCHEONS

Description	Part Number	Short Code	List Price
MODEL FP PUSH-ON/THREAD-OFF ESCUTCHEONS			
1/2" Chrome	6801412100	FPC	\$ 28.79
1/2" White	6801417200	FPW	\$ 28.79
1/2" Stainless Steel	6801411000	FPSS	\$ 131.85
3/4" Chrome	6801402100	FPLC	\$ 28.79
3/4" White	6801407200	FPLW	\$ 28.79
3/4" Stainless Steel	6801401000	FPLSS	\$ 131.85
MODEL F1 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800630001	GF1B	\$ 27.69
1/2" Chrome	6800600001	GF1C	\$ 14.92
1/2" White	6800640001	GF1W	\$ 14.92
1/2" Stainless Steel	6800610010	GF1SS	\$ 87.89
3/4" Brass	6801030000	GF1LB	\$ 27.69
3/4" Chrome	6801000000	GF1LC	\$ 14.92
3/4" White	6801040000	GF1LW	\$ 14.92
3/4" Stainless Steel	6800970010	GF1LSS	\$ 87.89
MODEL F1 ESCUTCHEON ONLY			
Brass	6800430000	BZESCF1	\$ 21.12
Chrome Bright	6800400000	CBESCF1	\$ 8.98
White	6800440000	WHESCF1	\$ 8.98
MODEL F1/F2 COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 16.53
1/2" Chrome Bright	6800500000	CBCOLLAR12	\$ 13.56
1/2" White	6800540000	WHCOLLAR12	\$ 13.56
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome Bright	6800560001	CBCOLLAR34	\$ 13.56
3/4" White	6800551003	WHCOLLAR34	\$ 13.56
ESCUTCHEON EXTENDER RING			
Chrome	6814002100	EERC	\$ 19.19
White	6814001500	EERW	\$ 20.45
MODEL F1 OR F2 EXTENDER RINGS			
4-1/2" Chrome	6814002100	EERC	\$ 19.19
4-1/2" White	6814001500	EERW	\$ 20.45
5-1/2" Chrome	6814042100	EERC5	\$ 19.19
5-1/2" White	6814041500	EERW5	\$ 20.45
FP / G5 / G4 / RFC / CCP / SWC COVERPLATE EXTENDER RINGS			
4-1/2" Chrome	6814022100	G4ERC	\$ 19.19
4-1/2" White	6814021800	G4ERW	\$ 20.45
5-1/2" Chrome	6814032100	G4ERC5	\$ 19.19
5-1/2" White	6814031800	G4ERW5	\$ 20.45

MODEL F2 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800830000	GF2B	\$ 27.69
1/2" Chrome	6800800000	GF2C	\$ 14.92
1/2" White	6800840000	GF2W	\$ 14.92
1/2" Stainless Steel	6800840010	GF2SS	\$ 87.89
3/4" Brass	6800880004	GF2LB	\$ 27.69
3/4" Chrome	6800880001	GF2LC	\$ 14.92
3/4" White	6800880005	GF2LW	\$ 14.92
3/4" Stainless Steel	6800880110	GF2LSS	\$ 87.89
ESCUTCHEON ONLY			
Brass	6800730000	BZESCF2	\$ 20.98
Chrome	6800700000	CBESCF2	\$ 13.52
White	6800740000	WHESCF2	\$ 13.52
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 16.53
1/2" Chrome	6800500000	CBCOLLAR12	\$ 13.56
1/2" White	6800540000	WHCOLLAR12	\$ 13.56
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome	6800560001	CBCOLLAR34	\$ 13.56
3/4" White	6800551003	WHCOLLAR34	\$ 13.56

Notes:

All SS Escutcheons are Type 316 Stainless Steel.
Other escutcheon finishes are available upon request.



B One Piece



C One Piece



HB Two Piece

ESCUTCHEONS (CONT.)

- Sprinkler Accessories

F1S ESCUTCHEON



F2S ESCUTCHEON

- See Bulletin 204

NEW



SURE-OFF TESTER

- See Bulletin 277

The simple way to determine if the system you are about to work on has been shut-off and drained!

1.800.431.1588
www.reliablesprinkler.com

Description	Size	Part Number	Short Code	List Price
MODEL B ONE PIECE TYPE 1/2"				
Bronze	1/2"	6800110000	BB	\$ 6.17
Chrome	1/2"	6800150000	BC	\$ 4.23
White	1/2"	6800120000	BW	\$ 4.77
Stainless Steel	1/2"	6800121002	BSS	\$ 52.76
MODEL B ONE PIECE TYPE 3/4"				
Bronze	3/4"	6800080000	BLB	\$ 6.51
Chrome	3/4"	6800070000	BLC	\$ 4.56
White	3/4"	6800090000	BLW	\$ 4.56
Stainless Steel	3/4"	6800091002	BLSS	\$ 52.76
MODEL C ONE PIECE TYPE 1/2"				
Bronze	1/2"	6800340000	CBB	\$ 47.00
Chrome	1/2"	6800350000	CC	\$ 4.52
White	1/2"	6800380000	CW	\$ 4.52
MODEL HB TWO PIECE TYPE 1/2"				
Bronze	1/2"	6800210000	HBB	\$ 10.75
Chrome	1/2"	6800270000	HBC	\$ 9.68
White	1/2"	6800200000	HBW	\$ 10.02
MODEL HB TWO PIECE TYPE 3/4"				
Bronze	3/4"	6800220000	HBLB	\$ 11.09
Chrome	3/4"	6800240000	HBLC	\$ 10.02
White	3/4"	6800250000	HBLW	\$ 10.75

Chrome	1/2" (15mm)	6801752100	F1SC	\$ 26.55
White	1/2" (15mm)	6801758700	F1SW	\$ 26.55
Chrome	3/4" (20mm)	6801762100	F1SLC	\$ 26.55
White	3/4" (20mm)	6801768700	F1SLW	\$ 26.55
MODEL F2S TWO PIECE RECESSED ESCUTCHEONS				
Chrome	1/2" (15mm)	6801772100	F2SC	\$ 26.55
White	1/2" (15mm)	6801778700	F2SW	\$ 26.55
Chrome	3/4" (20mm)	6801782100	F2SLC	\$ 26.55
White	3/4" (20mm)	6801788700	F2SLW	\$ 26.55

Description	Part Number	Short Code	List Price
PRESSURE TESTER			
Sure-Off Tester 1"	6501220000	SURE	\$ 2,120.98
Sure-Off Tester 1 1/4 - 1 1/2"	6501220002	SURE125	\$ 2,120.98
Sure-Off Tester 2"	6501220003	SURE2	\$ 2,120.98
Drill & Collar Assembly	6888000011		\$ 286.72
Guide Bushing, Drill, Reducer	94905000		\$ 94.99

Sprinkler Accessories

Description	Part Number	Short Code	List Price
SPRINKLER GUARDS & WATER SHIELD/GUARD ASSEMBLY			
C1,GUARD,SU,SP,HORIZONTAL,ZINC,FM ONLY	6802251400	GC1	\$ 15.26
C1,GUARD,SU,SP,HORIZONTAL,SS,FM ONLY	6802251000	GC1SS	\$ 152.48
C2,GUARD,DRY PENDENTS,UL/FM	6802201400	GC2	\$ 21.16
C3,GUARD,SHIELD,UPRIGHT-I,ZINC,UL/FM	6802501400	GC3	\$ 31.24
C5,GUARD/SHIELD KIT,SP-I,1/2,ZINC,FM	6802611412	GC51	\$ 43.66
C5,GUARD/SHIELD KIT,SP-I,3/4,ZINC,FM	6802611434	GC53	\$ 43.66
D1,GUARD,SU/SP/HORIZONTAL,UL/FM ZINC	6802251410	GD1	\$ 20.94
D3,GUARD/SHIELD KIT,SU-I,ZINC,UL ONLY	6802501410	GD3	\$ 24.76
D5,GUARD/SHIELD KIT,SP-I,1/2,ZINC,UL	6802631412	GD51	\$ 47.55
D5,GUARD/SHIELD KIT,SP-I,3/4,ZINC,UL	6802631434	GD53	\$ 47.55
D4,GUARD/SHIELD KIT,SP-I,1/2,ZINC,UL	6802621412	GD41	\$ 53.28
D4,GUARD/SHIELD KIT,SP-I,3/4,ZINC	6802621434	GD43	\$ 53.28
D-7 for use w/ GL112 Upright Intermediate	6802611614	GD7	\$ 24.76
D-8 for use w/ GL112 & GXLO Pendent	6802251714	GD8	\$ 20.94
D-9 for use w- GL112 & GXLO Pendent Intermediate	6802621714	GD91	\$ 47.55
D-6 for use w/ GXLO Upright Intermediate	6802611514	GD6	\$ 23.51
F-6,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026A1434	GF63	\$ 50.55
F-1,GUARD,ZINC	6802651400	GF1	\$ 20.94
F-2,GUARD,ZINC	6802661400	GF2	\$ 44.23
F-3,GUARD,SHIELD	6802671400	GF3	\$ 44.23
F-7,GUARD,ZINC	6802701400	GF7	\$ 44.23
F-8,GUARD/SHIELD KIT,1/2 NPS,ZINC	68026B1412	GF81	\$ 50.55
F-8,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026B1434	GF83	\$ 50.55
22 - (guard only) for use w/ HL22 ESFR	6802641422	G22	\$ 47.39
25 - (guard only) for use w/ N25 ESFR	6802641425	G25	\$ 47.39
D14,GUARD KIT,ZINC,SP,FM P22/P25	6802622514	GD14	\$ 47.39
RELIABLE MODEL RHB1 SPARE SPRINKLER STORAGE CABINET			
RASCO,RHB1 HEADBOX 3 COUNT	7M99005006	RHB3	\$ 90.50
RASCO,RHB1 HEADBOX 6 COUNT	7M99005007	RHB6	\$ 138.35
RASCO,RHB1 HEADBOX 6 COUNT ESFR	7M99005008	RHB6E	\$ 168.09
RASCO,RHB1 HEADBOX 12 COUNT	7M99005009	RHB12	\$ 153.87
RASCO,RHB1 HEADBOX 24 COUNT	7M99005010	RHB24	\$ 237.91
RASCO,RHB1 HEADBOX 36 COUNT	7M99005011	RHB36	\$ 329.71
A3 EMERGENCY CABINETS FOR RECESSED, CONCEALED & ZX SPK			
12 Capacity	6803200000	A312CAB	\$ 697.13

Sprinkler Accessories

Description	Part Number	Short Code	List Price
MODEL F SERIES SPRINKLER GUARDS & WATER SHIELD/GUARD ASSEMBLY			
F-1,GUARD,ZINC	6802651400	GF1	\$ 20.94
F-2,GUARD,ZINC	6802661400	GF2	\$ 44.23
F-3,GUARD,SHIELD	6802671400	GF3	\$ 44.23
F-4,GUARD,ZINC	6802681400	GF4	\$ 44.23
F-5,GUARD/SHIELD KIT,1/2 NPS,ZINC	6802691412	GF51	\$ 50.55
F-6,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026A1434	GF63	\$ 50.55
F-7,GUARD,ZINC	6802701400	GF7	\$ 44.23
F-8,GUARD/SHIELD KIT,1/2 NPS,ZINC	68026B1412	GF81	\$ 50.55
F-8,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026B1434	GF83	\$ 50.55
MODEL S WATER SHIELDS			
MODEL S-1 SHIELD,3.25,1/2-14NPS, GALV	88709001	S1SHIELD	\$ 18.13
MODEL S-2 SHIELD,3.25,3/4-14NPS, GALV	88709002	S2SHIELD	\$ 18.13
MODEL S-3 SHIELD,3.75,3/4-14NPS, GALV	88709003	S3SHIELD	\$ 18.13
MODEL S-5 SHIELD,4.5,1"NPS,GALV	887G9010	S5SHIELD	\$ 18.13

Notes:

For additional info see Bulletin 208



Description	Part Number	Short Code	List Price
STANDARD WRENCHES			
WRENCH,DS56	6880130002	WDS56	\$ 313.55
WRENCH,F3R,DRY	6880130001	WF3R	\$ 236.89
WRENCH,H,XLO/GL112,BLUE	6880070000	WH	\$ 179.42
WRENCH,J1,SPKR J112,J14,J17,ZINC.	6880090000	WJ1	\$ 179.42
WRENCH,W2(PENDENT,UPRIGHT,HSW)	6880050100	WW2	\$ 150.86
WRENCH, W8, RFC PLASTIC SERVICE WRENCH	6880050105	WW5	\$ 179.42
WRENCH,W13	6880108000	W13	\$ 212.52
WRENCH,W14	6880108100	W14	\$ 212.52
WRENCH,W15 (USE WITH GUARD)	6880108200	W15	\$ 212.52
WRENCH,W16	6880108300	W16	\$ 179.42
RECESSED & CONCEALED WRENCHES			
WRENCH,FC,CONCEALED	6880170020	WFC	\$ 450.07
WRENCH,G4,CONCEALED,ADJ,SP	6880170000	WG4	\$ 445.93
WRENCH,GFR2,RECESSED,CONCEALED,SP	6880060000	WGFR	\$ 447.68
WRENCH,G6 HSW SOCKET	6880101010	WG6	\$ 445.93
WRENCH,N,RECESSED	6880170030	WN	\$ 445.93
WRENCH,RC1 SOCKET,RECESSED	6880100000	WRC	\$ 447.68
WRENCH,RJ,J112/J112 REC CHROME	6880170032	WRJ	\$ 445.93
WRENCH,W1 (RECESSED PENDENT,CCP,& HSW)	6880100100	WW1	\$ 447.68
WRENCH W3 FOR WRENCH-ABLE PROTECTIVE CAP	6880100110	W3	\$ 450.07
WRENCH,W4,RECESSED,CONCEALED	6880100120	WW4	\$ 447.68
WRENCH,W10,WITH PROTECTIVE CAP,RFC49+	6880105000	W10	\$ 450.07
WRENCH,XLO2,REC,CONCEALED SP	6880070100	WXLO	\$ 235.15
WRENCH,XL,ZX,PENDENT	6880160000	WZXP	\$ 445.93
WRENCH,XL,ZX,HORIZONTAL	6880160010	WZXH	\$ 445.93
LIMITED SERVICE WRENCHES			
WRENCH,W8, RFC PLASTIC SERVICE WRENCH	6880103000	W8	\$ 279.08
WRENCH,W11,PLASTIC,RFC49+	6880107000	W11	\$ 279.08

Notes:

Each sprinkler bulletin will show required wrench

WRENCHES

- See Bulletin 205

PRINTED COVERPLATES


• See Bulletin 203



Slate Grey



Warm Maple



Dark Walnut



Silver Birch

Note: Please see Bulletin 203 for additional finishes

Part Number	Short Code	Temperature		Finish	List Price
MODEL G6 PRINTED COVERPLATES					
688721139A		135°F	57°C	Custom Ink	\$ 76.19
688721139B		135°F	57°C	White Wash	\$ 73.45
688721139C		135°F	57°C	Silver Birch	\$ 73.45
688721139D		135°F	57°C	Beige Birch	\$ 73.45
688721139E		135°F	57°C	Weathered Grey	\$ 73.45
688721139F		135°F	57°C	Slate Grey	\$ 73.45
688721139G		135°F	57°C	Golden Pine	\$ 73.45
688721139H		135°F	57°C	Red Oak	\$ 73.45
688721139J		135°F	57°C	Red Cherry	\$ 73.45
688721139K		135°F	57°C	Warm Maple	\$ 73.45
688721139M		135°F	57°C	Dark Walnut	\$ 73.45
688721139N		135°F	57°C	Espresso	\$ 73.45
688721139P		135°F	57°C	Rustic Beige	\$ 73.45
MODEL RFS42 PRINTED COVERPLATES					
688723139A		135°F	57°C	Custom Ink	\$ 76.90
688723139B		135°F	57°C	White Wash	\$ 74.12
688723139C		135°F	57°C	Silver Birch	\$ 74.12
688723139D		135°F	57°C	Beige Birch	\$ 74.12
688723139E		135°F	57°C	Weathered Grey	\$ 74.12
688723139F		135°F	57°C	Slate Grey	\$ 74.12
688723139G		135°F	57°C	Golden Pine	\$ 74.12
688723139H		135°F	57°C	Red Oak	\$ 74.12
688723139J		135°F	57°C	Red Cherry	\$ 74.12
688723139K		135°F	57°C	Warm Maple	\$ 74.12
688723139M		135°F	57°C	Dark Walnut	\$ 74.12
688723139N		135°F	57°C	Espresso	\$ 74.12
688723139P		135°F	57°C	Rustic Beige	\$ 74.12
MODEL G5 PRINTED COVERPLATES					
688727139A		135°F	57°C	Custom Ink	\$ 71.43
688727139B		135°F	57°C	White Wash	\$ 68.86
688727139C		135°F	57°C	Silver Birch	\$ 68.86
688727139D		135°F	57°C	Beige Birch	\$ 68.86
688727139E		135°F	57°C	Weathered Grey	\$ 68.86
688727139F		135°F	57°C	Slate Grey	\$ 68.86
688727139G		135°F	57°C	Golden Pine	\$ 68.86
688727139H		135°F	57°C	Red Oak	\$ 68.86
688727139J		135°F	57°C	Red Cherry	\$ 68.86
688727139K		135°F	57°C	Warm Maple	\$ 68.86
688727139M		135°F	57°C	Dark Walnut	\$ 68.86
688727139N		135°F	57°C	Espresso	\$ 68.86
688727139P		135°F	57°C	Rustic Beige	\$ 68.86
688727169A		165°F	74°C	Custom Ink	\$ 71.43
688727169B		165°F	74°C	White Wash	\$ 68.86
688727169C		165°F	74°C	Silver Birch	\$ 68.86
688727169D		165°F	74°C	Beige Birch	\$ 68.86
688727169E		165°F	74°C	Weathered Grey	\$ 68.86
688727169F		165°F	74°C	Slate Grey	\$ 68.86
688727169G		165°F	74°C	Golden Pine	\$ 68.86
688727169H		165°F	74°C	Red Oak	\$ 68.86
688727169J		165°F	74°C	Red Cherry	\$ 68.86
688727169K		165°F	74°C	Warm Maple	\$ 68.86
688727169M		165°F	74°C	Dark Walnut	\$ 68.86
688727169N		165°F	74°C	Espresso	\$ 68.86
688727169P		165°F	74°C	Rustic Beige	\$ 68.86



**MODEL G1
 CONCEALED
 REPLACEMENT
 COVERPLATES**

Part Number	Short Code	Temperature		Finish	List Price
MODEL G1 CONCEALED COVERPLATES - REQUIRED					
6887001311	CG10B	135°F	57°C	Finished Bronze	\$ 99.94
6887001321	CG10C	135°F	57°C	Chrome	\$ 73.35
6887001372	CG10W	135°F	57°C	White	\$ 73.35
6887001390	CG10SP	135°F	57°C	Special Paint	\$ 107.52
6887001611	CG11B	165°F	74°C	Finished Bronze	\$ 103.62
6887001621	CG11C	165°F	74°C	Chrome	\$ 73.35
6887001672	CG11W	165°F	74°C	White	\$ 73.35
6887001690	CG11SP	165°F	74°C	Special Paint	\$ 107.52

6880100000 WRC Requires Model RC1 Sprinkler Wrench \$ 447.68

***Model G1 Concealed Sprinkler is Obsolete.**
***Please note special paint is subject to a paint set-up charge.**