PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	€ 8,148.10
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		€ 8,888.83
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		€ 8,888.83
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		€ 8,888.83
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		€ 8,888.83
1-1/2" ISO7-1 Thread/Thread	6507608000		€ 8,888.83
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	€ 8,148.10
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		€ 8,888.83
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		€ 8,888.83
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		€ 8,888.83
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		€ 8,888.83
2" ISO7-1 Thread/Thread	6507628000		€ 8,888.83
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	€ 9,444.38
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		€ 9,444.38
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		€ 10,277.71
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		€ 10,277.71
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		€ 10,277.71
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		€ 10,277.71
2-1/2" ISO7-1 Thread/Thread	6507618000		€ 10,277.71
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	€ 9,444.38
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		€ 10,277.71
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		€ 10,277.71
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		€ 10,277.71
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		€ 10,277.71
3" ISO7-1 Thread/Thread	6507638000		€ 10,277.71
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	€ 11,296.22
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		€ 12,314.74
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		€ 12,314.74
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		€ 12,314.74
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	€ 13,888.80
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		€ 13,888.80
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		€ 15,277.68
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		€ 15,277.68
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		€ 15,277.68

Notes:
Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:
"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges
"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges
"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges
"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges