


Reliable[®] GROOVED

A Product You Can Depend On



Reliable[®]

Bringing Reliable Quality to Grooved

Reliable® GROOVED is the brand you can depend on.

Count on us to provide reliable quality products – but above all else – **exceptional service**. We have over 100 years of experience supplying fire protection products to businesses like yours across the world.

Reliable® GROOVED products operate under a 2-year limited warranty when installed correctly. Parts are **cULus Listed and FM Approved for use in systems with up to 300 psi pressure**.

Grooved Product Categories

- Angle Pad Rigid Couplings
- Flexible Couplings
- Reducing Couplings
- Mechanical Tees
- Fittings

Product Highlights

Grooved Couplings

- Rigid Couplings: 1" – 12"
- Flexible Couplings: 1" – 12"
- Reducing Couplings: 1 ½" – 8"
- Painted or Galvanized
- Gaskets: Dual-lubricated Grade-E EPDM; primary lubricant embedded in rubber prior to molding, secondary powder lubricant applied before shipping from factory
- Standard and Flush Gap gaskets available

Grooved Fittings


- Standard and Short Pattern Elbows and Tees
- Caps and Eccentric Caps
- End of Line Elbows
- Grooved Split Flanges and Grooved Flange Adapters
- Painted or Galvanized

Other Products

- Grooved and Threaded Outlet Mechanical Tees
- Grooved Split Flanges and Grooved Flange Adapters
- Dual-lubricated Grade-E EPDM

Reliable® GROOVED is the brand you can depend on.

Reliable® GROOVED Couplings



RGD1 ANGLE PAD RIGID COUPLING

1" – 12", Painted or Galvanized

Wet or Dry Systems

Pre-Lubricated Grade "E" EPDM, or Gap Seal



FLX1 Lightweight FLEXIBLE COUPLING

1" – 12", Painted or Galvanized

Wet or Dry Systems

Pre-Lubricated Grade "E" EPDM, or Gap Seal



RCD1 REDUCING COUPLING

1 ½" – 8", Painted or Galvanized

Reliable® GROOVED & Threaded Fittings



E901/TE1 STANDARD PATTERN ELBOWS AND TEES

1" – 12", Painted or Galvanized Finishes

Reducing, Cross, 45, 22½, 11¼ available



E90S1/TEsR1 SHORT PATTERN ELBOWS AND TEES

2" – 8", Painted or Galvanized Finishes



RCD1 GROOVED END CAPS

Painted or Galvanized Finishes



EOR1 END OF THE LINE ELBOW

Transition from grooved to female thread



MTT2/MTG1 MECHANICAL TEES

Quick and easy outlet installation without welding


Grooved or Threaded



G41 THREADED BRANCH TEE

Ideal for direct connection to sprinkler

Available Painted or Galvanized



FA1 GROOVED FLANGE ADAPTER

2" – 12", Painted or Galvanized

Allows direct connection of class 125 or 150 flange



Reliable® GROOVED

reliablesprinkler.com/grooved



© 2022 Reliable Automatic Sprinkler Co., Inc. 06/2022
Technical Modifications Reserved. P/N 99999RELBRR