



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar)
Rated Pressure
- Adjusted with Pilot
Operated Regulator
- Trim Includes Relief
Valve
- No Trim
Connections to
Cover
- cULus listed and
FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	A\$14,588.17
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		A\$15,914.37
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		A\$15,914.37
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		A\$15,914.37
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		A\$15,914.37
1-1/2" ISO7-1 Thread/Thread	6507608000		A\$15,914.37
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	A\$14,588.17
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		A\$15,914.37
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		A\$15,914.37
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		A\$15,914.37
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		A\$15,914.37
2" ISO7-1 Thread/Thread	6507628000		A\$15,914.37
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	A\$16,909.01
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		A\$16,909.01
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		A\$18,400.99
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		A\$18,400.99
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		A\$18,400.99
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		A\$18,400.99
2-1/2" ISO7-1 Thread/Thread	6507618000		A\$18,400.99
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	A\$16,909.01
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		A\$18,400.99
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		A\$18,400.99
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		A\$18,400.99
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		A\$18,400.99
3" ISO7-1 Thread/Thread	6507638000		A\$18,400.99
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	A\$20,224.51
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		A\$22,048.03
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		A\$22,048.03
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		A\$22,048.03
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	A\$24,866.20
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		A\$24,866.20
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		A\$27,352.82
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		A\$27,352.82
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		A\$27,352.82

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

- "0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges
- "1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges
- "2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges
- "3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges