PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	$10,357.60
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		$11,299.20
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		$11,299.20
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		$11,299.20
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		$11,299.20
1-1/2" ISO7-1 Thread/Thread	6507608000		$11,299.20
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	$10,357.60
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		$11,299.20
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		$11,299.20
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		$11,299.20
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		$11,299.20
2" ISO7-1 Thread/Thread	6507628000		$11,299.20
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	$12,005.40
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		$12,005.40
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		$13,064.70
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		$13,064.70
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		$13,064.70
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		$13,064.70
2-1/2" ISO7-1 Thread/Thread	6507618000		$13,064.70
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	$12,005.40
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		$13,064.70
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		$13,064.70
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		$13,064.70
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		$13,064.70
3" ISO7-1 Thread/Thread	6507638000		$13,064.70
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	$14,359.40
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		$15,654.10
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		$15,654.10
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		$15,654.10
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	$17,655.00
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		$17,655.00
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		$19,420.50
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		$19,420.50
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		$19,420.50

Notes:
Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:
"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges
"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges
"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges
"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges