MODEL PRV PRESSURE REGULATING **VALVE**

Performance Under Pressure

The Model PRV Pressure Regulating valve is an FM Approved, cULus Listed diaphragm-type valve used to reduce and regulate pressure in both flowing and non-flowing conditions.

Approved for 400 psi (27.6 bar) service

Features

- Compact trim
- FM Approved, cULus Listed
- Manufactured in the USA
- No trim connections to valve cover
- Field-adjustable output pressure
- Internally and externally coated with red oxide epoxy with a urethane coating to protect against UV damage

1½" (40 mm), 2" (50 mm), 2½" (65 mm), 76 mm, 3" (80 mm), 4" (100 mm), 6" (150 mm), 165 mm nominal sizes with multiple end configurations

Pressure Relief Valve

185 psi (12.8 bar), 260 psi (17.9 bar)







www.reliablesprinkler.com/prv

