

# MODEL DDV DIAPHRAGM DELUGE VALVE

## Performance Under Pressure

**UL Listed and FM Approved  
for up to 400 psi/27.6 bar.  
See Technical Bulletins 550 and 551  
for full product specifications.**

Diaphragm is the only moving internal valve component.

No trim connections to the valve cover for easy internal inspection

Compact footprint.

Six available trim options:

- Remote Resetting
- Remote Resetting/Pressure Regulating
- Dry Pilot/Pressure Regulating
- Electric Actuation
- Dry Pilot
- Wet Pilot

Sizes: 1½" (40 mm), 2" (50 mm),  
2½" (65 mm), 76 mm, 3" (80 mm),  
4" (100 mm), 6" (150 mm), 165 mm,  
8" (200 mm)



**Reliable®**



[www.reliablesprinkler.com/ddv](http://www.reliablesprinkler.com/ddv)